

PRODUCT SPECIFICATION

IR2CLQ4LA1

Camarque Self-Contained IP20 IR2 Surface

Catalogue Number **IR2CLQ4LA1**

GID **7TCA091170R0031**

Warranty **3 Year/s Refer to ABB warranty terms & conditions**

Power Supply System **Self-Contained (individual battery)**

Mounting Method/Form **Ceiling, Wall Surface**

Housing Material **Plastic**

Colour **White**

Dimensions (LxWxD) **348 x 348 x 122 mm**

Temperature Range **0 to 30°C**

Weight **2.2 Kg**

Emergency Duration (Hours) **3 Hours**

Battery **NiCd**

Monitoring Equipment **IR2 test**

Lamp **1+1 x 20 + 2W LED**

Emergency Light Output (Lumens) **1830/207**

Average Lifespan light source (Hours) **100000 Hours**

Light Colour/Temperature/CRI **White / 4000 / 80**

Degree of Protection **IP20**

Type of Legend **Not Applicable**

Exit Sign Viewing/Recognition Distance (m) **Not Applicable**

Nominal Voltage **220-240v AC 50/60Hz**

Power Consumption **25.8 VA / 23 Watts**

Current **Nominal: 108mA (mA) Inrush: 0.8A**

Accessories

CLQ/SR Semi-recessing kit

CLQ/GA Gold Angled Trim

CLQ/SA Silver Angled Trim

CLQ/WA White Angled Trim

CLQ/BKA Black Angled Trim



Luminaire with Silver Angled Trim
IR2CLQ4LA1 + CLQ/SA



Luminaire
IR2CLQ4LA1

