

## PRODUCT SPECIFICATION

# CTHY3LA2

## HYLED Self-Contained Open Area IP65 Naveo Surface

Catalogue Number **CTHY3LA2**  
 GID **7TCA091720R0080**  
 Warranty **4 Year/s Refer to ABB warranty terms & conditions**  
 Power Supply System **Self-Contained (individual battery)**  
 Mounting Method/Form **Ceiling, Wall Surface**  
 Housing Material **Plastic**  
 Colour **White**  
 Dimensions (LxWxD) **326 x 143 x 108.8 mm**  
 Temperature Range **0 to 25°C**  
 Weight **1.7 Kg**

Emergency Duration (Hours) **3 Hours**  
 Battery **NiCd**  
 Monitoring Equipment **Naveo®Pro**  
 Lamp **1 x 3.5W LED**  
 Emergency Light Output (Lumens) **400**  
 Average Lifespan light source (Hours) **60000 Hours**  
 Light Colour/Temperature/CRI **White / 6200 /**  
 Degree of Protection **IP65 IK8**

Type of Legend **Not Applicable**  
 Exit Sign Viewing/Recognition Distance (m) **Not Applicable**  
 Nominal Voltage **220-240v AC 50Hz**  
 Power Consumption **15 VA / 7 Watts**  
 Current **Nominal: 65mA (mA)**

## Accessories

**HY-MBK** Wall Mounting/ Coupling bracket kit  
**HY-RKIT** Recessing kit



**Recessed Mount**  
 CTHY3LA2 + HY-RKIT



**Surface Mount**  
 CTHY3LA2

IoT

IP  
65



LED  
•••

