

PRODUCT SPECIFICATION

WWA1LS1X

Weatherforce 110-230V AC/DC 27M IP65 Surface

Catalogue Number **WWA1LS1X**
GID **7TCA091130R0551**
Warranty **3 Year/s Refer to ABB warranty terms & conditions**
Power Supply System **Mains / Slave Operation**
Mounting Method/Form **Ceiling, Wall Surface**
Housing Material **Metal**
Colour **White**
Dimensions (LxWxD) **400 x 140 x 100 mm**
Temperature Range **0 to 40°C**
Weight **1.2 Kg**

Emergency Duration (Hours) **Mains / Central Battery Hours**
Battery **Mains / Central Battery**
Monitoring Equipment **None**
Lamp **1 x 2W LED**
Emergency Light Output (Lumens) **207**
Average Lifespan light source (Hours) **100000 Hours**
Light Colour/Temperature/CRI **White / 4000 / 80**
Degree of Protection **IP65 IK10**

Type of Legend **Single or Double Sided**
Exit Sign Viewing/Recognition Distance (m) **27**
Nominal Voltage **110-230v AC/DC 0-60Hz**
Power Consumption **3.4 VA / 3.2 Watts**
Current **Nominal: 13.59mA (mA) Inrush: 1.1A**

Accessories

XEN2/2DV32 Double sided Diffuser with Down+Down ISO7010 Legend
XEN3/6DV32 Double sided Diffuser with Left+Right ISO7010 Legend
XEN5/5DV32 Double sided Diffuser with Up+Up ISO7010 Legend

XB10DV32 Double sided Diffuser with Blank+Arabic English Legend
XB11DV32 Double sided Diffuser with Arabic English+Arabic English Legend
XB23DV32 Double sided Diffuser with Arabic English Left+Arabic English Right Legend
XB50DV32 Double sided Diffuser with Blank+Arabic English Up Legend
XB66DV32 Double sided Diffuser with Arabic English Down+Arabic English Down Legend

BBZ Semi recessing bezel White



Double Sided Exit Sign
WWA1LS1X + XEN2/2DV32

