

TECHNICAL DATA SHEET

Stanilite®

Platinum batten LED - 4 foot



| Catalogue no. | Description | | | |
|-------------------------------------|---|--|--|--|
| EM products | , | | | |
| PBL4AC46L | AC46L Platinum batten LED AC 4600 lumen | | | |
| PBL4EM46LM | Platinum batten LED EM 4600 lumens maintained | | | |
| Spare parts | | | | |
| 03-01227 Battery LiFePO4 6.4V 3.0Ah | | | | |


Range

Platinum range

Product group


Batten LED






















- · Large terminal block for quick and easy installation
- · Lanyard attached to the lamp and base body makes installation easier
- Frosted diffuser for even light distribution
- Insect proof sealed LED module
- · Can be surface mounted or suspended
- AC efficacy typically 120 lumens/watt
- Ambient operating temperature; AC 0° C to $+40^{\circ}$ C and EM +10°C to +40°C



| -· · | | | | |
|--------------|---------------------------------------|-----------------------------|--------|--|
| Dimensions | | | | |
| | Length | Width | Height | |
| | 1200mm | 80mm | 65mm | |
| Weight | · | | , | |
| | Model | Weight | , | |
| | AC | 2.1kg | | |
| | EM | 2.8kg | | |
| Construction | · | | , | |
| | Part | Construction | | |
| | Base body | Powder coated steel | | |
| | Lamp body, end cap and diffuser | Polycarbonate and aluminium | | |

| Light source | ' | ' | | | |
|-------------------|-------|-------------|----------------|---------|---------------------------|
| | Model | Light sour | ce | | |
| | AC/EM | LED strips | | | |
| Power consumption | | | | | |
| | Model | Normal | S/A off | Standby | |
| | AC | 38W | OW | N/A | |
| | EM | 43W | 5W | N/A | |
| | | | | | Note: Preliminary results |
| Photometrics | | | ' | | |
| | Model | Class | Classification | | |
| | EM | Co | D80 | | |
| | | C 90 | D50 | | |
| | | | | | Note: Preliminary results |

Note:

- AC designed to comply with AS/NZS60598.2.1 and meet relevant Australian EMC standards EM designed to comply with AS2293.3 and meet relevant Australian EMC standards