Pedestals

EH3 - Accessories

DIN bases

			DIN 00	DIN 0	DIN 1	DIN 2	DIN 3
		HxWxD	900x450x310	900x585x310	900x780x310	900x1110x310	900x1430x310
	Factory-	Type	EH3BEXEH	EH3BE0EH	EH3BE1EH	EH3BE2EH	-
	assembled	Order code	4TBE843390N0100	4TBE843391N0100	4TBE843392N0100	4TBE843393C0100	
	Polyester base, supplied in kit	Туре	EH3SEXEI	EH3SE0EI	EH3SE1EI	EH3SE2EI	EH3SE3EI
	form, RAL 7035	Order code	4TBE843204R0100	4TBE843205R0100	4TBE843206R0100	4TBE843207R0100	4TBE843208R010
	Base made from recycled material Construction kit.	Туре	EH3SEXEH	EH3SE0EH	EH3SE1EH	EH3SE2EH	EH3SE3EH
	Color similar to RAL 7035	Order code	4TBE842098C0100	4TBE842099R0100	4TBE842100R0100	4TBE842101R0100	4TBE843144R0100
	Concrete base	Туре	EH3REXEJ	EH3RE0EJ	EH3RE1EJ	EH3RE2EJ	EH3RE3EJ
	(with metal front plate)	Order code	4TBE843272C0100	4TBE843273C0100	4TBE843274C0100	4TBE843275C0100	4TBE843276C0100
ounting pla	tes						
		HxWxD	665x350x5	665x485x5	665x680x5	705×1000×5	705×1340×5
	Pertinax mounting plate		EH3M8XEH	EH3M80EH	EH3M81EH	EH3M82EH	EH3M83EI
	piace	Order code	4TBE843681C0100	4TBE843024C0100	4TBE843044C0100	4TBE843057C0100	4TBE843067C0100
		HxWxD	915x350x5	915x485x5	915x680x5	955×1000×5	955x1340x5
	Height 1125 mm	Type	EH3M9XEH	EH3M90EH	EH3M91EH	EH3M92EH	EH3M93EI
		Order code	4TBE843682C0100	4TBE843070C0100	4TBE843071C0100	4TBE843072C0100	4TBE843256C0100
لم		HxWxD			915x680x10	955 x 1000 x 10	955 x 1340 x 10
		Type	-	-	EH3M91EHP	EH3M92EHP	EH3M93EH
		Order code			4TBE783325C0100	4TBE783326C0100	4TBE783327C0100
Base plates							
		HxWxD	427x285x3	562x285x3	757x285x3	1086x285x3	1416x285x3
70	Base plate	Type	EH3PEXEI	EH3PE0EH	EH3PE1EH	EH3PE2EH	EH3PE3EH
(a a)	3 mm polyester with securing screws	Order code	4TBE843683C0100	4TBE843300C0100	4TBE843301C0100	4TBE843302C0100	4TBE843303C0100
Wall mountin	a kit						
Wan in our can	g Kit	В.	555	710	885	1215	1545
6	Wall mounting kit Two Alu C profiles	Туре	EH3WEXEI	EH3WE0EH	EH3WE1EH	EH3WE2EH	EH3WE3EH
N	with brackets for wall mounting	Order code	4TBE843684N0100	4TBE843441C0100	4TBE843442C0100	4TBE843443C0100	4TBE843444N0100

Pedestals

EH3 - Accessories

EH3 - Accessories

Product	Type	Order code	Pack		
Locks with profile half cylin	der				
	With 2 keys ,	With 2 keys , V2432-E			
	EH3AEECI	4TBE843001C0100	1		
	Spare keys fo	or EH3AEECI			
1	PS832022	4TBP832022C0100	2		
	With 1 squar	With 1 square key, 8 mm			
39.5	EH3AEEQH	4TBE843002C0100	1		
	With an 8 mm triangular key				
	EH3AEETH	4TBE843003C0100	1		
	With 2 keys A434				
- 20	EH3UAECI	4TBE843248C0100	1		
4 30	Spare keys upo	n request.			

Product	Type	Order code	Pack
	. In a Labour		


Vandal proof nameplate holder

Can be placed on every flat surface, by drilling two holes Ø 5.5 mm; the identification window is used as a drill template. Steady against vandalism; it keeps its total isolation . Possibility to write on manually and/or to use the standard lettering systems; the maximal letter height is 18 mm. Usefull dimensions of letters: 18 x 143. Outside dimensions: 30 x 183 x 5



EH3AEEE4 4TBE843304C0100 1

Diagram holder



DIN A4 - W x H = 325 x 180 mm				
AR811516	4TBX811516R0100	1		
DIN A5 - W x H= 155 x 225 mm				
PS832000	4TBP832000C0100	1		

Handle



Handle for lock with a profile half cylinder EH3EESH

4TBE843000C0100 1

Spare part

IP44 ventilation grille





Suitable for a ventilation opening Includes 2 grilles and 4 nylon nails. Total insulation. RAL 7035

4TBP832019C0100 1

Set of 2 pieces

PS832019

Double closure handle



For two locks with profile half cylinder

EH3AEEDH 4TBE783042C0100 1

Spare part (Note: for after-market installation, an operation is required on the door mechanism).

Threaded insert



M8 threaded insert Dodge-type for rear wall and door. 4TBO851026C0100 100 Punch for inserting M8 threaded barrel. **EHUOEEEG** 4TBC844039C0100 1

Concrete base (kit)



Size: DIN00 **EH3REXEJ** 4TBE843272C0100 1 Size: DINO EH3RE0EJ 4TBE843273C0100 1 Size: DIN1 EH3RE1EJ 4TBE843274C0100 1 Size: DIN2 EH3RE2EJ 4TBE843275C0100 1 Size: DIN3 EH3RE3EJ 4TBE843276C0100 1

Pedestals

EH3 - Accessories

EH3 - Accessories

Product

Front plate with opening for temporary connections on DIN base			
May be used with DIN -00 to -2 bases in RAL 7035 color (EH3SEXEI-			
EH3SE2EI). This front plate is not standard and must be ordered in			
addition. The standard closed front plate may be used if it is not			
necessary for temporary connections. The DIN 3 base is standard w	vith		
a front plate for temporary connections. The front plates on the fro	nt and		
rear are secured by screws.			

Туре

Order code

Pack





Product	Туре	Order code	Pack	
Locking plate	'			
	Double door lock with 3-point lock for reinforcement.			
E. T.	EH3AEECY	4TBE843560N010	0 1	
77				

Door locking



May be installed on left-hand or righthand swinging doors. Mounting by drilling 2 holes in the interior profile. Includes mounting parts.

EH3AEEEZ 4TBE843007C0100 1

Screws (replacement parts)



Clip-in button
Hilo 5.8 x 16 mm

EH3AEEEN 4TBE843556C0100 1

Clip-in button
Hilo 5.8 x 22 mm

EH3OEEEG 4TBE890278C0100 1

Mounting bolts for mounting plates (replacement parts)



DIN 00-0-1
EH3AE0EI 4TBE843566C0100 1
DIN 2-3
EH3AE2EI 4TBE843567C0100 1