

Pedestals

EH1 - Small pedestal



EH1C14VH

Applications

- Cable television
- Gas distribution
- Telecommunication (surface connections)
- Camping sites

Standard: EN / IEC 62208

Specifications

- Small outdoor enclosure with integrated base.
- Hood grey colour RAL 7035:
 - ventilated version in polyester or thermoplastic engineering polymer,
 - non ventilated version in hot moulded, glass fibre reinforced polyester,
 - blackened triangular zamac locking screws, vandalproof and for all seasons.
- - Degrees of protection:
 - IP43 for the non ventilated hoods,
 - IP23 for the ventilated hoods.
- According to IEC 60529:
 - protection degree against external mechanical impacts according to EN/IEC 62262.
- IK09 polyester hood
- IK10 thermoplastic hood
- Rated insulation voltage Ui 690V
- Base in high density polyethylene (HDPE) RAL 9005
- Base resists a ground temperature of -50°C
- The upper part of the base serves as a mounting plate and is provided with three slots for fixation points.
- Moulded-in indication of burial depth.
- Option: 2432E lock.
- Easy to install by one person only (weight: 4.5 kg).
- Dimensions: 753×385×270 (H×W×D in mm)

EH1 - Column cabinet

| Type | Type | Order code | Pack |
|--|------------|-----------------|------|
| (H x W x D) 753 x 385 x 270 mm | | | |
| Ventilated | EH1C14VHNA | 4TBE841037C0100 | 1 |
| Non-ventilated | EH1C14NH | 4TBE841038C0100 | 1 |
| Accessories | | | |
| The protective hood may be opened by an 8 mm triangular key. | PS832027 | 4TBP832027C0100 | 1 |
| Ventilated protective hood | EH1AEEV3 | 4TBE841039N0100 | 1 |
| Non-ventilated protective hood | EH1AEEEN4 | 4TBE841040N0100 | 1 |
| Closure for older models | EH1AEEEI | 4TBE841041N0100 | 1 |

