



中国国家强制性产品认证证书

证书编号: 2003010304064033

委托人名称、地址

ABB STOTZ-KONTAKT GmbH
Eppelheimer Strasse 82 69123 Heidelberg Germany

生产者(制造商)名称、地址

ABB STOTZ-KONTAKT GmbH
Eppelheimer Strasse 82 69123 Heidelberg Germany

生产企业名称、地址

ABB STOTZ-KONTAKT GmbH
Eppelheimer Strasse 82 69123 Heidelberg Germany

产品名称和系列、规格、型号

交流接触器

B6, BC6, B7, BC7, VB6, VBC6, VB7, VBC7; 型号解释详见附件

产品标准和技术要求

GB 14048.4-2010

上述产品符合强制性产品认证实施规则
CNCA-C03-02: 2014的要求, 特发此证。

发证日期: 2017年03月08日

有效期至: 2022年03月08日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

本证书为变更证书, 证书首次颁发日期: 2003年07月22日

本证书的相关信息可通过国家认监委网站www.cnca.gov.cn查询



主任:

中国质量认证中心

中国·北京·南四环西路188号9区 100070

<http://www.cqc.com.cn>



Q 1624679



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

No. : 2003010304064033

NAME AND ADDRESS OF THE APPLICANT

ABB STOTZ-KONTAKT GmbH
Eppelheimer Strasse 82 69123 Heidelberg Germany

NAME AND ADDRESS OF THE MANUFACTURER

ABB STOTZ-KONTAKT GmbH
Eppelheimer Strasse 82 69123 Heidelberg Germany

NAME AND ADDRESS OF THE FACTORY

ABB STOTZ-KONTAKT GmbH
Eppelheimer Strasse 82 69123 Heidelberg Germany

NAME, MODEL AND SPECIFICATION

AC Contactor

B6, BC6, B7, BC7, VB6, VBC6, VB7, VBC7; see appendix for details

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB 14048.4-2010

This is to certify that the above mentioned products have met the requirements of implementation rules for compulsory certification(REF NO. CNCA-C03-02:2014).

Date of issue: Mar.08,2017 Date of expiry: Mar.08,2022

Validity of this certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Date of original certification: Jul.22,2003

This certificate can be verified through CNCA's website: www.cnca.gov.cn



President:

Wang Kejiao

CHINA QUALITY CERTIFICATION CENTRE

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China

<http://www.cqc.com.cn>



Q 1624679



中国国家强制性产品认证证书

附录:

第 1 页 共 3 页

证书编号: 2003010304064033

纸号: 1624679

B6, BC6, B7, BC7, VB6, VBC6, VB7, VBC7

Ui: 690V; Ith: 20A;

B6, BC6, VB6, VBC6, B6...F:

AC-1: Ue/le: 220/230/240/380/400V/16A, 440/500V/12A, 690V/6A;

B7, BC7, VB7, VBC7, B7...F:

AC-1: Ue/le: 220/230/240/380/400/440V/20A, 500V/12A, 690V/6A;

B6...P, B7...P:

AC-1: Ue/le: 220/230/240/380/400/440/500V/12A, 690V/6A;

B6, BC6, VB6, VBC6:

AC-3: Ue/le: 400V/8.5A, 500V/6.5A, 690V/3.5A;

DC-1: Ue/le: 24V/16A, 110V/5A, 220V/0.8A;

DC-3: Ue/le: 24V/16A, 110V/1.5A, 220V/0.25A;

B7, BC7, VB7, VBC7:

AC-3: Ue/le: 400V/11.5A, 500V/9A, 690V/3.5A;

DC-1: Ue/le: 24V/16A, 110V/5A, 220V/0.8A;

DC-3: Ue/le: 24V/16A, 110V/1.5A, 220V/0.25A;

Us: DC:17-32V, 24V, 48V, 110-125V, 220-240V,

AC:24V, 48V, 110-127V, 220-240V, 380-415V, 500V;

极数: 3P, 4P; IP20;

配用辅助触头: (本体)

Ith: 6A;

AC-15: Ue/le: 24-240V/4A, 380-440V/3A, 480-500V/2A;

DC-13: Ue/le: 24V/2.5A, 125V/0.7A, 250V/0.4A

1NO,1NC

注: 此附录与证书同时使用时有效。



主 任:

中国质量认证中心

中国·北京·南四环西路188号9区 100070

<http://www.cqc.com.cn>





中国国家强制性产品认证证书

附录:

第 2 页 共 3 页

证书编号: 2003010304064033

纸号: 1624679

型号解释:

V	B	C	6	A	3.0	01	P	-1.4
1	2	3	4	5	6	7	8	9

1 V Reverser

Blank Standard

2 Main designation

3 C stands for DC coil,

Blank stands for AC coil,

4 Contactor series type (B6 series or B7 series)

5 A Reverser with locking device

D DC version with integrated diode

S DC version with integrated diode and varistor

Blank Standard

6 Number of main contacts (30, 40 or 22), 30-3NO, 40-4NO, 22- 2NO/2NC

7 Type of auxiliary contacts (01, 10 or 00), 01-1NC, 10-NO and 00-none

8 Terminal

blank: standard screw version

F: Quick connect terminals

P: Pin terminal

9 coil consumption(blank or1.4 or1.7 or 2.4 or 2.8)

Blank normal product

1.4 low consumption

1.7 low consumption

2.4 low consumption

2.8 low consumption

注: 此附录与证书同时使用时有效。



主任:

中国质量认证中心

中国·北京·南四环西路188号9区100070

<http://www.cqc.com.cn>





中国国家强制性产品认证证书

附录:

第 3 页 共 3 页

证书编号: 2003010304064033

纸号: 1624679

V	B	C	6	A-	30-	01-	P	-1.4
1	2	3	4	5	6	7	8	9

- 1 V 可逆起动产品
空白 标准产品
- 2 B 系列型号描述
- 3 C 直流线圈
空白 交流线圈
- 4 6 B6 系列
7 B7 系列
- 5 A 闭锁装置的可逆起动产品
D 直流线圈内置二极管
S 直流线圈内置二极管和压敏电阻
空白 标准产品
- 6 主触点数量类型 (30 or 40 or 22), 30-3 常开, 40-4 常开, 22-2 常开, 2 常闭
- 7 辅助触点数量类型 (01 or 10 or 00), 01-1 常闭, 10-1 常开, 00-无
- 8 接线方式
空白 标准螺钉
-P 焊接
-F 插接
- 9 线圈功耗 coil consumption(blank or 1.4 or 1.7 or 2.4 or 2.8)
空白 标准产品
1.4 低功耗
1.7 低功耗
2.4 低功耗
2.8 低功耗

注: 此附录与证书同时使用时有效。



主任:

中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>

