








SACE Tmax XT

Ekip Maintenance Module MM - XT5

XT5





	F	W		F	W
 A	1		 D		1
 B		1			
 C	1	1	E A CURA DEL CLIENTE AT CUSTOMER'S EXPENSE ZU LASTEN DES KUNDEN A LA CHARGE DU CLIENT A CARGO DEL CLIENTE 由客户承担 F THERMOSHRINKING INSULATING SHEATH FOR SERVICE TEMPERATURES OF: -55 ÷ +135C° SINGLE POLE CABLE UL758 STYLE 1385 18 AWG  THERMOSHRINKING INSULATING SHEATH FOR SERVICE TEMPERATURES OF: -55 ÷ +135C° 	5	1

1

F 2



F






3

4

F







8

F 9



F



10

F 11



W



12

W 13



W






14

W 15

W







21

W 22

W



23

W 24

W

