




Current Rating

60 Amperes

FC Voltage Ratings

2- and 3-pole — 600/347 Vac, 500 Vdc

FB Voltage Ratings

2- and 3-pole — 600/347 Vac

1-pole — 347 Vac

Frequency Rating

50/60 Hertz

Molded Case Circuit Breaker with Thermal-Magnetic Trip Unit

Record Plus™ Types FC & FB

Long Time Delay and Instantaneous Time-Current Curves

Enclosure-Compensated

Curves show enclosure-compensated circuit breaker in open air, 40°C ambient, wired with conductors of corresponding rating, no prior load. For all other ambients, use rating shift index at top of sheet.

DES021

Adjustments

Long-time delay thermal trip: not adjustable. Instantaneous magnetic trip: not adjustable.

Note 1: Current limiting range, please refer to inset curve.