

H81365P.-A

EN
CN

2 1WU21000 MD 055100

1. Go to the online webpage by scanning the QR code.

2. Click on the “Downloads” tab to find the documents.

English

Mini video outdoor station

Operation

1

Ring indicator

Indicator flashes slowly: ringing

Indicator flashes quickly: busy line

2

Call indicator

3

Unlock indicator

4

Speaker and microphone integration

5

Round pushbutton module with IC card reader

Connection

1

Connector for the sensor used for door status detection

2

Connector for exit button

3

Plug-in clamps (LOCK...AGND) for door opener

4

Plug-in clamps (COM...NC...NO) for floating output

5

Plug-in clamps (DC+...GND) for standalone power supply

6

LAN (PoE)

7

N/A

Technical data

Rating voltage	24 V
Operating voltage range	20-27 V
Rating current	27 V , 310 mA
	24 V , 350 mA
Operating temperature	-40 °C...+70 °C
Product dimensions	105 x 180 x 43 mm
Camera type	CMOS
Camera viewing angle	104°
Power supply for door opener	15 V , 4A impulse, max. 250 mA holding

Floating output for door opener

30 V , 3 A

IP level

IP 54

IK level

IK 07

中文

可视小主机

操作

1

振铃指示灯

指示灯慢闪: 振铃

指示灯快闪: 占线

2

呼叫指示灯

3

开锁指示灯

4

麦克风与扬声器

5

圆按键模块带 IC 刷卡功能

接口

1

门状态检测接口

2

出门按钮接口

3

开锁接口 (LOCK...AGND)

4

继电器开锁接口 (COM...NC...NO)

5

独立电源接口 (DC+...GND)

6

LAN (PoE)

7

N/A

技术参数

额定电压	24 V
工作电压范围	20-27 V
额定电流	27 V , 310 mA
	24 V , 350 mA
工作温度	-40 °C ... +70 °C
产品尺寸	105 x 180 x 43 mm
摄像头类型	CMOS
摄像头可视角度	104°
功率开锁	15 V , 4 A 脉冲, 最大保持电流 250 mA

信号开锁

30 V , 3 A

IP 等级

IP 54

IK 等级

IK 07