

## COPYSTICK

## For fast and accurate repeat drive programming

Compatibility:

This Option is suitable for use on the following product range: ACS250 & ACS255 Drives

Note:

Parameters can only be copied between drives of the same product range and power rating (size).

 Part No.
 3AUA0000135608

 Model No.
 RCCS-01

 Document No.
 3AXD10000706810

Literature Fulfilment number. ACS255-PNMU01U-EN\_REVA

ABB Oy AC Drives P.O. Box 184 FI-00381 HELSINKI FINLAND

82-STICK-ABB\_V2



Drive display message to show the status for certain operation

PR55-r: COPYSTICK read / stored the drive parameters successfully.

U5-Loc: COPYSTICK is locked; attempting to read parameter from the drive with COPYSTICK lock switch on.

FR L-r: COPYSTICK failed to read parameter from the drive.

PR55-L: COPYSTICK transferred parameters to the drive (write parameters to drive) successfully.

FR L-P: The power rating of the parameters saved in the COPYSTICK does not match the power-rating of the drive to be

programmed.

FR L-E: COPYSTICK failed to transfer parameter set to drive.


no-dAL: No parameter data saved in the COPYSTICK.

dr-Loc: Drive parameters have been locked and cannot accept new parameter settings. Unlock drive parameter set.

dradin: Drive is running and cannot accept new parameter settings. Stop drive operation before programming.

EYPE-E: Parameters for Drive type saved in COPYSTICK do not match the drive type to be programmed (write operation only).

EYPE-F: COPYSTICK currently doesn't support the drive type to be programmed.



## COPYSTICK

## For fast and accurate repeat drive programming

Compatibility:

This Option is suitable for use on the following product range:

ACS250 & ACS255 Drives

Note:

Parameters can only be copied between drives of the same product range and power rating (size).

 Part No.
 3AUA0000135608

 Model No.
 RCCS-01

 Document No.
 3AXD10000706810

Literature Fulfilment number. ACS255-PNMU01U-EN\_REVA

ABB Oy AC Drives P.O. Box 184 FI-00381 HELSINKI FINLAND

www.abb.com/drives

82-STICK-ABB\_V2



Drive display message to show the status for certain operation

PR55-r: COPYSTICK read / stored the drive parameters successfully.

D5-Loc : COPYSTICK is locked; attempting to read parameter from the drive with COPYSTICK lock switch on.

FR L-r: COPYSTICK failed to read parameter from the drive.

PR55- L: COPYSTICK transferred parameters to the drive (write parameters to drive) successfully.

FR L-P: The power rating of the parameters saved in the COPYSTICK does not match the power-rating of the drive to be programmed.

FR L-L: COPYSTICK failed to transfer parameter set to drive.

no-dAL: No parameter data saved in the COPYSTICK.

dr-Loc: Drive parameters have been locked and cannot accept new parameter settings. Unlock drive parameter set.

dr-rlln: Drive is running and cannot accept new parameter settings. Stop drive operation before programming.

EYPE-E: Parameters for Drive type saved in COPYSTICK do not match the drive type to be programmed (write operation only).

EYPE-F: COPYSTICK currently doesn't support the drive type to be programmed.

