

PRODUCT SPECIFICATION

CTCLQ4LA1

Camarque Self-Contained IP20 Naveo Surface

Catalogue Number **CTCLQ4LA1**
 GID **7TCA091180R0347**
 Warranty **3 Year/s Refer to ABB warranty terms & conditions**
 Power Supply System **Self-Contained (individual battery)**
 Mounting Method/Form **Ceiling, Wall Surface**
 Housing Material **Plastic**
 Colour **White**
 Dimensions (LxWxD) **348 x 348 x 122 mm**
 Temperature Range **0 to 30°C**
 Weight **2.2 Kg**

Emergency Duration (Hours) **3 Hours**
 Battery **NiCd**
 Monitoring Equipment **Naveo®Pro**
 Lamp **1+1 x 20 + 2W LED**
 Emergency Light Output (Lumens) **1830/207**
 Average Lifespan light source (Hours) **100000 Hours**
 Light Colour/Temperature/CRI **White / 4000 / 80**
 Degree of Protection **IP20**

Type of Legend **Not Applicable**
 Exit Sign Viewing/Recognition Distance (m) **Not Applicable**
 Nominal Voltage **220-240v AC 50/60Hz**
 Power Consumption **25.8 VA / 23 Watts**
 Current **Nominal: 108mA (mA) Inrush: 0.8A**

Accessories

CLQ/SR Semi-recessing kit

CLQ/GA Gold Angled Trim

CLQ/SA Silver Angled Trim

CLQ/WA White Angled Trim

CLQ/BKA Black Angled Trim



Luminaire with Silver Angled Trim
CTCLQ4LA1 + CLQ/SA



Luminaire
CTCLQ4LA1

IoT

