

PRODUCT SPECIFICATION

LTCLQ1LA1

Camarque 230v AC IP20 EMEX Test Surface

Catalogue Number **LTCLQ1LA1**
 GID **7TCA091140R0536**
 Warranty **3 Year/s Refer to ABB warranty terms & conditions**
 Power Supply System **Mains / Slave Operation**
 Mounting Method/Form **Ceiling, Wall Surface**
 Housing Material **Plastic**
 Colour **White**
 Dimensions (LxWxD) **348 x 348 x 122 mm**
 Temperature Range **0 to 40°C**
 Weight **1.8 Kg**

Emergency Duration (Hours) **Mains / Central Battery Hours**
 Battery **Mains / Central Battery**
 Monitoring Equipment **EMEX test**
 Lamp **1 x 20W LED**
 Emergency Light Output (Lumens) **1830**
 Average Lifespan light source (Hours) **100000 Hours**
 Light Colour/Temperature/CRI **White / 4000 / 80**
 Degree of Protection **IP20**

Type of Legend **Not Applicable**
 Exit Sign Viewing/Recognition Distance (m) **Not Applicable**
 Nominal Voltage **220-240v AC 50/60Hz**
 Power Consumption **20.8 VA / 19.5 Watts**
 Current **Nominal: 86mA (mA) Inrush: 0.8A**

Accessories

CLQ/SR Semi-recessing kit

CLQ/GA Gold Angled Trim

CLQ/SA Silver Angled Trim

CLQ/WA White Angled Trim

CLQ/BKA Black Angled Trim



Luminaire with Silver Angled Trim
 LTCLQ1LA1 + CLQ/SA



Luminaire
 LTCLQ1LA1

