

PRODUCT SPECIFICATION

CTHY3LE2

HYLED Self-Contained Escape Route IP65 Naveo Surface

Catalogue Number **CTHY3LE2**
 GID **7TCA091720R0081**
 Warranty **4 Year/s Refer to ABB warranty terms & conditions**
 Power Supply System **Self-Contained (individual battery)**
 Mounting Method/Form **Ceiling, Wall Surface**
 Housing Material **Plastic**
 Colour **White**
 Dimensions (LxWxD) **326 x 143 x 108.8 mm**
 Temperature Range **0 to 25°C**
 Weight **1.7 Kg**

Emergency Duration (Hours) **3 Hours**
 Battery **NiCd**
 Monitoring Equipment **Naveo®Pro**
 Lamp **1 x 3.5W LED**
 Emergency Light Output (Lumens) **400**
 Average Lifespan light source (Hours) **60000 Hours**
 Light Colour/Temperature/CRI **White / 6200 /**
 Degree of Protection **IP65 IK8**

Type of Legend **Not Applicable**
 Exit Sign Viewing/Recognition Distance (m) **Not Applicable**
 Nominal Voltage **220-240v AC 50Hz**
 Power Consumption **15 VA / 7 Watts**
 Current **Nominal: 65mA (mA)**

Accessories

HY-MBK Wall Mounting/ Coupling bracket kit

HY-RKIT Recessing kit



Recessed Mount
CTHY3LE2 + HY-RKIT



Surface Mount
CTHY3LE2

IoT

IP
65



LED
●●●

