

PRODUCT SPECIFICATION

HY1LA2LTC

HYLED 230v AC Open Area IP65 EMEX Test Surface

Catalogue Number **HY1LA2LTC**
 GID **7TCA091720R0120**
 Warranty **4 Year/s Refer to ABB warranty terms & conditions**
 Power Supply System **Mains / Slave Operation**
 Mounting Method/Form **Ceiling, Wall Surface**
 Housing Material **Plastic**
 Colour **White**
 Dimensions (LxWxD) **326 x 143 x 108.8 mm**
 Temperature Range **0 to 40°C**
 Weight **1.7 Kg**

Emergency Duration (Hours) **Mains / Central Battery Hours**
 Battery **Mains / Central Battery**
 Monitoring Equipment **EMEX test**
 Lamp **1 x 7W LED**
 Emergency Light Output (Lumens) **1000**
 Average Lifespan light source (Hours) **60000 Hours**
 Light Colour/Temperature/CRI **White / 6200 /**
 Degree of Protection **IP65 IK8**

Type of Legend **Not Applicable**
 Exit Sign Viewing/Recognition Distance (m) **Not Applicable**
 Nominal Voltage **220-240v AC 50/60Hz**
 Power Consumption **15.5 VA / 14 Watts**
 Current **Nominal: 67mA (mA) Inrush: 16A**

Accessories

HY-MBK Wall Mounting/ Coupling bracket kit
HY-RKIT Recessing kit



Recessed Mount
 HY1LA2LTC + HY-RKIT



Surface Mount
 HY1LA2LTC

