

Stanilite®

Platinum exit LED edgelit recessed Nexus®



Range

Platinum range

Product group

Exit LED edgelit



Features

- High emergency classification
- LED technology 100,000 hours plus lamp life
- Low power consumption and LED light source for reduced operation and maintenance costs
- Advanced charging technology combined with Lithium iron phosphate battery for long life and low maintenance
- Nexus monitored, either cabled or wireless
- Architecturally pleasing slim line design
- One-box solution, overall light weight and snap n' clip mechanism allows for quick and easy installation
- Suits ceiling thickness 1mm-19mm
- 2m flex and plug included
- Includes all pictograph diffuser options
- Adaptor plate available for use when upgrading older edgelit exit signs - see accessories

Catalogue no.	Description
Nexus products	
PLRNXSLEDP	Platinum exit LED edgelit recessed Nexus LX pictograph
PLRNRFLEDP	Platinum exit LED edgelit recessed Nexus RF pictograph
Accessories	
PLRLEDADAPTOR	Cover plate for retrofitting
Spare parts	
03-01304P	Battery pack 2wr LiFePO4 3.2V 1.5Ah
03-01332	Battery pack_V1 2wr LiFePO4 6.4V 1.5Ah
03-01308PB	Battery pack_V2 3wr LiFePO4 3.2V 1.5Ah



Dimensions		
Item	Length	Width
Face plate	370mm	120mm
Ceiling cutout	348mm	97mm
Weight		
Model	Weight	
Nexus LX/RF	1.9kg	
Construction		
Part	Construction	
Body and diffuser	Plastic	

Light source		
Model	Light source	
Nexus LX/RF	Multiple LED 0.7W	

Power consumption		
Model	Power consumption	
Nexus LX/RF	2.4W	

Note: Preliminary results

Photometrics			
Model	Class		Classification
Nexus LX/RF	C0		D3.2
	C90		E2

Note: Preliminary results

Note:
- Designed to comply with AS2293 and meet relevant Australian EMC standards