

Stanilite®

Platinum exit LED weatherproof Nexus®



Range

Platinum range

Product group

Exit LED



Features

- LED technology 100,000 hours plus lamp life
- Low power consumption and LED light source for reduced operation and maintenance costs
- IP65 weatherproof enclosure
- Advanced charging technology combined with Lithium iron phosphate battery for long life and low maintenance
- Nexus monitored, either cabled or wireless
- UV stabilised vandal resistant (IK08) polycarbonate cover
- Surface mount
- Removable gear tray for easy installation and maintenance

Catalogue no.	Description
Nexus products	
PWEXNXSLEDP-1	Platinum exit LED weatherproof Nexus LX picto
PWEXNXSLEDP-2	Platinum exit LED weatherproof Nexus LX <picto
PWEXNXSLEDP-3	Platinum exit LED weatherproof Nexus LX picto>
PWEXNRFLEDP-1	Platinum exit LED weatherproof Nexus RF picto
PWEXNRFLEDP-2	Platinum exit LED weatherproof Nexus RF <picto
PWEXNRFLEDP-3	Platinum exit LED weatherproof Nexus RF picto>
Spare parts	
03-01301P	Battery pack 2wr LiFePO4 3.2V 3.2Ah
03-01310PB	Battery pack_V2 3wr LiFePO4 3.2V 3.2Ah
31-PWE1	DIFF PWEX PICTO 24m INC CLR LID
31-PWE2	DIFF PWEX <PICTO 24m INC CLR LID
31-PWE3	DIFF PWEX PICTO> 24m INC CLR LID



Dimensions			
	Length	Width	Height
	380mm	130mm	190mm
Weight			
	Model	Weight	
	Nexus LX/RF	2.0kg	
Construction			
	Part	Construction	
	Enclosure	Polycarbonate	
	Gear tray	White powder coated zinc steel	

Light source			
	Model	Light source	
	Nexus LX/RF	Multiple LED 1.6W	

Power consumption			
	Model	Power consumption	
	Nexus LX/RF	3.2W	

Photometrics			
	Model	Class	Classification
	Nexus LX/RF	C0	D1.25
		C90	C1.25

Note: Preliminary results

Note:

- Designed to comply with AS2293 and meet relevant Australian EMC standards