

Exit LED Quickfit®

Signature exit LED Quickfit frame only



Image indicative only

Range

Signature range

Product group

Exit LED Quickfit®

Features

- 3 year warranty
- LED technology 100,000 hours lamp life
- Low power consumption and LED light source for reduced operation and maintenance costs
- High temperature NiCad batteries
- Frame only version of the Quickfit LED exit 100K sign (PQFLEDS)
- Designed for upgrading of installed Quickfit® product - retrofit capability; fits into any existing Quickfit mounting bracket
- Supplied less mounting bracket and diffusers - the frame will accept existing MQF/PQF diffusers and backplates



Standard products

Catalogue no.	Description
PQFLEDS-FR	Quickfit LED exit 100K frame only

Spare parts

Catalogue no.	Description
03-YPMA001	Battery 3 cell NiCad 3.6V 1.6Ah

Dimensions

Length	Width	Height
379mm	72mm	212mm

Construction

Part	Construction
Body	UV/FR ABS body

Light source

Model	Light source
Standard	Multiple LED 1.2W

Power consumption

Model	Power consumption
Standard	4.0W

Photometrics

Model	Class	Classification
Standard	C0	D3.2
	C90	D3.2

Note: Designed to comply with AS2293 and meet relevant Australian EMC standards

For more information please contact:

ABB Australia Pty Limited

Phone: 1300 666 595

Fax: 1300 666 594

E-mail: AU-ABB-Stanilite@abb.com

www.stanilite.com.au

Note: We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilisation of its contents – in whole or in parts – is forbidden without prior written consent of ABB.

Copyright © 2016 ABB
All rights reserved