

TECHNICAL DATA SHEET

# Stanilite®

## Nexus® LX user pack including server with LCD 22" monitor



### Range

Non-standard range

### Product group

Nexus LX components



### Features

- Intel i3-8109U Processor (3Ghz base and 3.6Ghz turbo frequency)
- 4GB DDR4 SO DIMM memory
- 240GB SSD hard drive
- Intel Iris Plus graphics 655
- HDMI 2.0, 4 x USB 3.0, 1 x Thunderbolt 3, SD card slot, GBLAN, wireless AC, 22" LCD monitor, keyboard and mouse
- Windows 10 Professional
- Nexus LX software and Nexus user and technical guide on USB stick

Catalogue no.	Description
<b>Nexus products</b>	
NXSLXSERVERLCD	Nexus LX user pack

<b>Dimensions</b>			
	Length	Width	Height
	117mm	112mm	51mm

<b>U10 lonworks I/F module and HXSROUT/2</b>	
Item	Details
U10	The U10 lonworks is a high performance lonworks interface sheath: "STANILITE NCS"

Includes:

- U10 USB lonworks IF module TP FT 10
- HXSROUT/2 router NX5 TP78/FTT10

### Note:

- Designed to comply with AS2293 and meet relevant Australian EMC standards

---

ABB Australia Pty Limited  
Phone: 1800 60 20 20  
E-mail: AU-ABB-Stanilite@abb.com

**[www.stanilite.com.au](http://www.stanilite.com.au)**

---

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilisation of its contents – in whole or in parts – is forbidden without prior written consent of ABB.  
Copyright © 2019 ABB  
All rights reserved