

TECHNICAL DATA SHEET

Stanilite®

Platinum exit LED edgelit recessed Nexus®



Catalogue no.	Description
Nexus products	
SGPLRNRFLDP	Platinum exit LED edgelit recessed Nexus RF pictograph
Accessories	
PLRLEDADAPTOR	Cover plate for retrofitting
Spare parts	
03-01308P	Battery LiFePO4 3.2V 1.5Ah

Range

Platinum range

Product group

Exit LED edgelit



Features

- High emergency classification
- LED technology 100,000 hours plus lamp life
- Low power consumption and LED light source for reduced operation and maintenance costs
- Advanced charging technology combined with Lithium iron phosphate battery for long life and low maintenance
- Nexus monitored, wireless
- RF frequency range 920 - 925 MHz
- Architecturally pleasing slim line design
- One-box solution, overall light weight and snap n' clip mechanism allows for quick and easy installation
- Suits ceiling thickness 1mm-19mm
- 2m flex and plug included
- Includes all pictograph diffuser options
- Adaptor plate available for use when upgrading older edgelit exit signs - see accessories



Dimensions			
	Item	Length	Width
	Face plate	370mm	120mm
	Ceiling cutout	348mm	97mm
Weight			
	Model	Weight	
	Nexus RF	1.9kg	
Construction			
	Part	Construction	
	Body and diffuser	Plastic	

Light source			
	Model	Light source	
	Nexus RF	Multiple LED 0.7W	
Power consumption			
	Model	Power consumption	
	Nexus RF	2.4W	
Note: Preliminary results			
Photometrics			
	Model	Class	Classification
	Nexus RF	C0	D3.2
		C90	E2
Note: Preliminary results			

Note:

- Complies to IEC60598.2.22 and AS2293