



中国国家强制性产品认证证书

证书编号: 2019010307261879

委托人名称、地址

ABB S. p. A.

Via Vittor Pisani 16-20124 Milano (MI)-Italy

生产者(制造商)名称、地址

ABB S. p. A.

Viale dell'Industria 18-20010 Vittuone (MI)-Italy

生产企业名称、地址

ABB S. p. A.

Via Ardeatina 2491-00040 Santa Palomba (RM)-意大利

产品名称和系列、规格、型号

剩余电流动作断路器

DS201T;详见附件

产品标准和技术要求

GB/T16917.1-2014;GB/T16917.21-2008

上述产品符合强制性产品认证实施规则 CNCA-C03-02:2014 的要求,
特发此证。

发证日期: 2019 年 12 月 19 日 有效期至: 2024 年 12 月 19 日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

本证书的相关信息可通过国家认监委网站 www.cnca.gov.cn 查询

经中国合格评定国家认可委员会认可 CNAS C001-P



主任:

陆楠



中国质量认证中心



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO.: 2019010307261879

NAME AND ADDRESS OF THE APPLICANT

ABB S.p.A.
Via Vittor Pisani 16-20124 Milano (MI)-Italy

NAME AND ADDRESS OF THE MANUFACTURER

ABB S.p.A.
Viale dell'Industria 18-20010 Vittuone (MI)-Italy

NAME AND ADDRESS OF THE FACTORY

ABB S.p.A.
Via Ardeatina 2491-00040 Santa Palomba (RM) - Italy

PRODUCT NAME, MODEL AND SPECIFICATION

Residual Current Operated Circuit-breakers with Integral Overcurrent Protection
for household and similar uses (RCBOs)
DS201T; See the appendix

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T16917.1-2014; GB/T16917.21-2008

This is to certify that the above mentioned product(s) complies with the requirements of
implementation rules for compulsory certification (REFNO.CNCA-C03-02:2014).

Valid from: Dec.19,2019

Valid until: Dec.19,2024

The validity of the certificate is subject to positive result of the regular follow up
inspection by issuing certification body until the expiry date.

The certificate information is available through CNCA's website: www.cnca.gov.cn
Accredited by China National Accreditation Service for Conformity Assessment CNAS C001-P



President:

Lu Mei



CHINA QUALITY CERTIFICATION CENTRE

<http://www.cqc.com.cn>

Section 9, No. 188, Nanshuan Xilu, Beijing 100070 P. R. China

Tel: +86 10 83886666

Q 2495374



中国国家强制性产品认证证书

附 录

第 1 页 共 2 页

证书编号: 2019010307261879

纸 号: 2495374

DS201T

U_{imp} : 4kV;

U_i : 500V;

U_e : AC230V;

I_n : 6A, 10A, 13A, 16A, 20A, 25A, 32A, 40A;

瞬时脱扣类型: B 型, C 型;

$I_{\Delta n}$: 30 mA;

额定剩余动作类型: A 型; 电磁式;

$I_{\Delta m}$: 4500 A (32A, 40A), 6000A (6A, 10A, 13A, 16A, 20A, 25A);

I_{cs} : 6000A;

I_{cn} : 6000A;

极数: 1P+N (1 个保护极, N 极可开闭);

适用于隔离;

适用频率: 50/60Hz

注: 此附录与证书同时使用时有效。



主 任:

陆 楠



中国质量认证中心



中国国家强制性产品认证证书

附 录

证书编号: 2019010307261879

第 2 页 共 2 页

纸 号: 2495374

型号解释:

<u>DS 201T</u>	<u>C</u>	<u>16</u>	<u>0.03</u>	<u>A</u>
1	2	3	4	5

- 1——DS201T 系列
- 2——瞬时脱扣特性:
 - B—B 特性
 - C—C 特性
- 3——额定电流:
 - 6A, 10A, 13A, 16A, 20A, 25A, 32A, 40A
- 4——额定剩余动作电流 $I_{\Delta n}$
 - 0.03 A
- 5——剩余电流动作特性:
 - A—A 型; AP-R - AP-R 型

注: 此附录与证书同时使用时有效。



主 任:

陆 楠



中国质量认证中心