

TECHNICAL DATA SHEET

Stanilite®

Economy Spitfire® LED surface mount - black version



Catalogue no.	Description	
EM products		
ECOSPITFIREBOX-BLK	Economy Spitfire LED surface mount - black version	
Spare parts		
03-01233	Battery LiFePO4 6.4V 1.5Ah	

Range

Economy range

Product group

Spitfire LED




Features


• Quick and easy installation



- Superior photometric classification
- LED technology 100,000 hours plus lamp life



- · Lithium iron phosphate battery
- Surface mount
- Non-maintained operation
- Ingress protection IP54
- Insulation class II
- $\bullet\,$ SAA tested and approved



Dimensions				
	Length	Width	Height	
	130mm	130mm	30mm	
Weight		,	'	
	Model	Weight	Weight	
	EM	1.0kg		
Construction		,		
	Part	Constructi	Construction	
	Body	Polycarbon	Polycarbonate	

Light source		'	
	Model	Light source	
	EM	2W	
Power consumption			
	Model	Power consumption	
	EM	1.0W average	
			Note: Preliminary results
Photometrics		·	
	Model	Class	Classification
	EM	Co	D40
		C90	D40

Note:

⁻ Designed to comply with AS2293 and meet relevant Australian EMC standards