# **ELXC-LP Series**

144

Combination unit with light bar



### Construction

- Off-white UV stabilized thermoplastic enclosure
- 6 inch EXIT lettering legend, available in red or green
- Universal single or double face
- Field selectable chevrons
- Light bar consumes 4.5 watts
- Adjustable lens for optimal light distribution
- 5VA Flame retardant thermoplastic
- Remote capacity for (1) EF12D/LED or (2) EF12/LED

### Mounting

- Surface and wall mount
- Canopy included for end or ceiling mount application
- Universal J-box mounting

### Electronics

- 120/27760 Hz
- 4.8V long life nickel cadmium battery
- Approvals

## • UL 924 listed


• Damp location 32°F to 122°F (0°C to 50°C)

### Warranty (subject to proper installation and maintenance)

• Unit has a three-year warranty Detailed warranty terms located on page 178 of the catalog or online at:

www.emergi-lite.com/usa/files/EL\_Warranty.pdf

#### Photometric performance



### Power consumption

Model	AC specs	DC specs
ELXC-LPR	120/277VAC, 7.5W	4.8V nickel-cadmium battery (min. 90 minutes)
ELXC-LPG	120/277VAC, 7.5W	4.8V nickel-cadmium battery (min. 90 minutes)

Accessories (order as a separate item)

Suffix
WG1-E
WG5-E
P*WT <sup>1</sup>

<sup>1</sup>Specify length when ordering


\_

# How to order

Series	I	Legend color
ELXC-LP= Combination	5	<b>R</b> = RED <b>G</b> = GREEN
Example: ELXC-LPG	,	

### Dimensions

Dimensions are approximate and subject to change.



# **EF12D-LED Series**

Thermoplastic square LED Outdoor remote heads



# Features

- Multi-volt 3.6, 6 or 12V, 3W in total
- Thermoplastic housing and aluminum canopy with fully adjustable LED heads
- Available only in gray 2-heads configuration
- Suitable for outdoor, wet location applications
- Wall or ceiling mount
- -4°F to 122°F
- UL 924 Listed


Warranty (subject to proper installation and maintenance)

- Unit has a three-year warranty
- Detailed warranty terms located on page 178 or online at: www.emergi-lite.com/usa/files/EL\_Warranty.pdf

### Dimensions

Dimensions are approximate and subject to change.

## EF12-LED Series



How to order – EF12D-LED Series

Series	# of lamp	Options
EF12	Blank= Single head D= Double head	-LED = Thermoplastic square LED head

0000 0000 0000

Example: EF12D-LED

# Photometric performance

