Total[™] Edge Series

Single and double face, surface and recessed mount edge-lit exit sign



Construction

- Extruded aluminum housing
- High grade acrylic panel
- 6 inch EXIT lettering legend, available in red or green
- Field-selectable chevrons
- Satin aluminum housing
- Optional Advanced Diagnostics

Mounting

Universal mount model

- Pivoting panel design allows for recessed, surface, wall or ceiling mount installation
- A ratcheting mechanism allows the panel to be set in place from 0° to 180° for wall or sloped ceiling mounting
- Canopy included for surface wall, end or ceiling mount application
- Easy snap in backbox with securing trim plate allow for sheet rock ceiling installation
- Trim plate, 27 inch adjustable T-bar hangers and a junction box included for recessed application

Approvals

- UL 924 listed
- Damp location 50°F to 104°F (10°C to 40°F)
- Meets NFPA101 (Life Safety Code) NFPA 70 NEC and OSHA illumination standards

Warranty (subject to proper installation and maintenance)

 Unit has a three-year warranty Detailed warranty terms located on page 178 of the catalog or online at: www.emergi-lite.com/usa/files/EL_Warranty.pdf

Accessories (order as a separate item)

Suffix
850.0107-E
P*WT
P*BK
081886-E


¹Required for use with pendant


Dimensions

Dimensions are approximate and subject to change.

3-1/2

Power consumption





Model			AC specs		DC specs
Red	AC only	120VAC, 60Hz	2.0-2.6W	-	-
		277VAC, 60Hz	2.6-3.1W	-	-
	Self-powered	120VAC, 60Hz	2.0-2.6W	Ni-Cd battery	Min. 90 minutes
		277VAC, 60Hz	2.6-3.1W	Ni-Cd battery	Min. 90 minutes
Green	AC anh	120VAC, 60Hz	2.8-3.3W	_	_
	AC only	277VAC, 60Hz	3.5-4W	_	_
		120VAC, 60Hz	2.8-3.3W	Ni-Cd battery	Min. 90 minutes
	Self-powered	277VAC, 60Hz	3.5-4W	Ni-Cd battery	Min. 90 minutes

How to order

Series	Color	Legend	Options
PA= AC Only	R= Red on	6= 6" EXIT single	-AD= Advanced
PN= Self-powered	mirror	and double	Diagnostics ¹
PA2 = AC only dual circuit	G= Green on	face with	
Example: PNR6-AD	mirror	universal chevrons	

¹Only available on self-powered models

AD