ELXN400 LED Series

Low energy and low maintenance for moderate budget application



Housing

- UV stabilized thermoplastic body
- Fully adjustable and reversible Cluster[™] LED glare-free heads
- 6 inch EXIT lettering legend, available in red or green
- Universal faces (2 faceplates, 1 backplate)
- · Field selectable chevrons

Mounting

- Surface mount
- Canopy included for ceiling mount applications
- Universal J-box mounting finishes

Type of battery

• 3.6V nickel-cadmium battery

Lamp head source

• White LED 3.6V-1.8W each

- Electronics
- Optional Advanced Diagnostics
- 120/277 60Hz

Approvals


- UL 924 listed
- Damp location 50°F to 104°F (10°C to 40°F)
- UL 94, 5VA flame rated

Warranty (subject to proper installation and maintenance)

Unit has a three-year warranty
 Detailed warranty terms located on page 178 or online at:
 www.emergi-lite.com/usa/files/EL_Warranty.pdf


Photometric performance

Spacing center-to-center (feet)	
7' mounting height	15' mounting height
15'	4'



Dimensions

Dimensions are approximate and subject to change.



Power consumption

	Current (A) / Power (W) 120/277VAC, 60Hz	
Model		
ELXN400R-2LED	0.044/0.017A	
ELXN400G-2LED	0.032/0.015A	
ELXN400R-2LEDR	0.037/4.06A	
ELXN400G-2LEDR	0.036/3.8A	
ELXN400R_2LEDR-AD	0.038/0.017A	
ELXN400G_2LEDR-AD	0.038/0.017A	

Accessories (order as a separate item)

Description	Suffix
Wire guard	WG10-E
Battery	850.0110-E

How to order

Series	Legend color	Lamp	Options	Color
ELXN400= ELX	R= Red exit	-2LED= Round LED array	Blank= No option	Blank= White
Combo Series	G = Green exit		R= 3.6W remote capacity to power one double head remote ¹ R-AD= 3.6W remote capacity to power one double head dedicated remote with	B = Black
Example: ELXN40	OR-2LED		Advanced-Diagnostics ¹	

 $^{^{1}\}text{Remote capacity can only be used to power the EF43D or EF44D remote fixtures or to extend the battery units emergency run time beyond the standard 90 minutes.$

EF43D & EF44D Series

Photometric performance

Spacing center-to-center (feet)

7' mounting height

15'

Low energy and low maintenance for moderate budget application

15' mounting height




The Cluster™ LED EF43D-LED or EF44D-LEDWP

The Cluster™ LED EF43D-LED or EF44D-LEDWP Remote head can ONLY be powered from the ELXN400 LED series combo or EL-2LED battery units of the same family. Used for internal $\,$ or external applications, the indoor remote head draws 3.6V-3.6W and Weather-Proof head draws 3.6V-3.8W.




 $\label{lem:decomposition} \mbox{Dimensions are approximate and subject to change.}$











How to order

es #	# of lamps	Lamp	Option
	D = 2	-LED= round	Blank= Indoor
I= Outdoor		LED	remote
weather-proof		array	WP= Outdoor
series			weather
			proof remote
mple: EF43D-LED			
mple: EF43D-LED			proorre