ELX400 SQL LED Series

Combination unit with tool-less field-adjustable heads to accommodate top mount requirements





Construction

- UV stabilized thermoplastic body
- Fully adjustable Square LED glare-free heads
- 6 inch EXIT lettering legend, available in red or green
- · Field selectable chevrons

Mounting

- Surface mount
- Canopy included for ceiling mount applications / end mount
- · Universal J-box mounting

Finishes

• White

Remote capacity/combination units

 ELXN400-2SQLR and ELXN400-2SQLRAD feature a 3.6V Ni-Cd battery with two 1W LED heads attached as well as 3W of remote capacity for EF12D-LED or EF47DSQL

Lamp head source

- 3.6V-1W LED head
- Lamp heads are fully adjustable to top or side with no tools required.
- 100 lumens per head

Electronics

- Optional Advanced Diagnostics
- 120/277 60Hz

Approvals


- UL 924 listed
- Damp location 50°F to 104°F (10°C to 40°F)
- UL 94, 5VA flame rated

Warranty (subject to proper installation and maintenance)

Unit has a three-year warranty
Detailed warranty terms located on page 178 or online at:
www.emergi-lite.com/usa/files/EL_Warranty.pdf


Photometric performance


Spacing center-to-center (feet)	
7 ft. mounting height	15 ft. mounting height
13'	4'




Dimensions

Dimensions are approximate and subject to change.







Power consumption

Description	
120/277VAC, 60Hz, 0.048A	

Accessories (order as a separate item)

Description	Suffix	
Wire guard (heads in any position)	WG10-E	
Replacement battery for ELXN400-2SQL	022434-E	
Replacement battery ELXN400-2SQLR	022435-E	
Replacement battery ELXN400-2SQLRAD	022435-E	

How to order

Series	Legend	Heads	Options
ELXN400	R= Red	-2SQL= 1WLED	Blank= No option
	G= Green		R= Remote capacity to power one double head remote ¹
Example: ELXN400R-2SQLR-AD			R-AD= Remote capacity to power one double head dedicated remote with Advanced-Diagnostics ¹

¹To be used with EF47DSQL or EF12D-LED only