ELX Remote Capable Exit Series

Economical, thermoplastic LED exit sign





Construction

- UV stabilized thermoplastic body
- 6 inch exit lettering legend, available in red or green
- · Field selectable chevrons
- · Standard universal faces

Mounting


- Surface mount
- Canopy included for end or ceiling mount applications
- Universal J-box mounting

Finishes

• White

Dimensions

Dimensions are approximate and subject to change.



Electronics

- Optional Advanced Diagnostics
- 120/277 60Hz

Approvals

- UL 924 listed
- Damp location 50°F to 104°F (10°C to 40°F)
- UL 94, 5VA flame rated

Warranty (subject to proper installation and maintenance)

Unit has a three-year warranty
Detailed warranty terms located on page 178 or online at:
www.emergi-lite.com/usa/files/EL_Warranty.pdf

Power consumption

Description	
120/277VAC, 60Hz maximum 2.5W	

Accessories (order as a separate item)

Description	Suffix
Wire guard (wall mount)	WG1-E
Wire guard (ceiling mount and end mount)	WG5-E
Battery	820.0106-E
Pendant white	P*WT
Pendant black	P*BK

How to order

Series	Legend color	Options
ELX400= AC only	RN= Red	Blank= No options
ELXN400 = Self powered	GN= Green	-AD= Advanced Diagnostics
		-RAD= Advanced Diagnostics
		with 3.6V-3.6W remote
Example: EL VN400BN E	DAD.	capacity ¹

 $^{^{1}}$ Available with red legend only, compatible with EF47DSQL or EF12D-LED