TYPE:CATALOG #:	
NOTES:	_
NOTES.	





Chicago CCE-LED Series Steel LED Exit Sign



Features

- White LED light source
- Constructed of 20-gauge steel with an off-white finish and glass panels
- Canopy supplied for top or end-mount
- Universal Knockout pattern on back plate for wall mount
- Single or Double face
- 4.8V Long-life, maintenance-free Nickel-Cadmium rechargeable on Self-Powered model
- Dual voltage 120/277, 60Hz
- Automatic solid-state charger recharges battery in 24hours
- 120 minutes run time in Emergency mode
- UL listed for Damp-Location 68°F to 122°F (20°C to 50°C)
- Meets UL 924, NFPA 101 Life safety code, NEC, OSHA, local and state codes
- City of Chicago Approved
- 3 Year Full warranty


Detailed warranty terms located at: www.emergi-lite.com/usa/files/EL_Warranty.pdf

Power Consumption Chart

Model	del AC Specs				DC Specs
CCER	120/277VAC, 60HZ	5W	0.1A/ 0.05A	-	-
CCENR	120/277VAC, 60HZ	5W	0.1A/ 0.05A	Ni-Cd	Minimum 120 minutes

Dimensions

Dimensions are approximate and subject to change.



Arrow (Chevron) Designation







Arrow Right Arrow Left

Double Arrow

Represents each side of a double face panel.

*Wording and chevrons not to scale. For illustration purposes only.

How to Order

SERIES	LEGEND COLOR	LEGEND STYLE
ICE= AC Only ICEN= Self-Powered	R= Red	#2A= Single Face, STAIRS, No Arrow #17A= Double Face, STAIRS, No Arrow #3= Single Face, EXIT, No Arrow #18= Double Face, EXIT, No Arrow #5A= Single Face, STAIRS

Example: CCENR#2A



