Survive-All™ EF39 Series and EF40 Series

EF39 NEMA-4X & NSF certified EF40 vandal resistant





Description


- EF39 and EF39P NEMA-4X and NSF certified indoor or outdoor use
- EF39 and EF39P NEMA-4X and NSF certified with choice of fully gasketed cast aluminum or plastic back plate¹
- EF40 and EF40P vandal resistant for Indoor USE with choice of fully gasketed cast aluminum or plastic back plate
- EF39 and EF39P NEMA-4X and NSF Certified comes standard with Phillips head screws and tamper proof screws
- Available as single or double MR16 LED lamp size remote lighting fixture Include clear polycarbonate UV and impact resistant cover
- Includes clear polycarbonate UV and impact resistant cover

Lamp type

· Choice of MR16 LED lamp wattages

Photometric performance

	Spacing center-to-center	
Lamp	7' mounting height	15' mounting height
LA	39'	34'
LB	74'	57'
LG	49'	39'
LI	68'	54'
LJ	89'	80'
LL	51'	39'



Mounting

- Surface mount
- · Universal J-box mounting approval

Approval

- UL 924 listed
- Vandal resistant¹
- NEMA-4X¹
- NSF Rated


¹EF39P and EF39 units are NEMA-4X Certified when installed using a circular NEMA-4X rated junction box (sold separately by Thomas&Betts under product number 091647-E)


Warranty

Unit has a five-year limited warranty
Detailed warranty terms located on page 178 or online at:
www.emergi-lite.com/usa/files/EL_Warranty.pdf

Dimensions

Dimensions are approximate and subject to change.





Accessories

Description	Suffix
Additional special bit for tamper-proof screws	690.0454-E

How to order EF39 Series

Lamp type/ wattage	Lamp type	Option
(LA)= 6V-4W, MR16 LED	Blank= White	SM= Mounting plate
(LB)= 6V-5W, MR16 LED	-BK= Black	
(LG)= 12V-4W, MR16 LED	-GY = Gray	
(LI)= 12V-5W, MR16 LED		
(LJ)= 12V-6W, MR16 LED		
(LL)= 24V-4W, MR16 LED		
	(LA)= 6V-4W, MR16 LED (LB)= 6V-5W, MR16 LED (LG)= 12V-4W, MR16 LED (LI)= 12V-5W, MR16 LED (LJ)= 12V-6W, MR16 LED	(LA)= 6V-4W, MR16 LED Blank= White (LB)= 6V-5W, MR16 LED -BK= Black (LG)= 12V-4W, MR16 LED -GY= Gray (LI)= 12V-5W, MR16 LED (LJ)= 12V-6W, MR16 LED

Series	Lamp type/ wattage	Lamp type
EF39= Die-cast back plate single head NEMA-4X	(LA)= 6V-4W, MR16 LED	Blank= White
EF39D= Die-cast back plate double head NEMA-4X	(LB)= 6V-5W, MR16 LED	-BK = Black
	(LG)= 12V-4W, MR16 LED	-GY = Gray
	(LI)= 12V-5W, MR16 LED	
	(LJ)= 12V-6W, MR16 LED	
Example: EF39P(LG)-BK	(LL)= 24V-4W, MR16 LED	

_

How to order EF40 Series

Series	Lamp type/ wattage	Lamp type	Options
EF40P = All polycarbonate back plate single head	(LA)= 6V-4W, MR16 LED	Blank= White	Blank= No options
EF40PD= All polycarbonate plate double head	(LB)= 6V-5W, MR16 LED	-BK = Black	T= Tamper proof
	(LG)= 12V-4W, MR16 LED	-GY = Gray	screws
	(LI)= 12V-5W, MR16 LED		SM = Mounting
	(LJ)= 12V-6W, MR16 LED		plate
Example: EF40P(LG)	(LL)= 24V-4W, MR16 LED		

Series	Lamp type/ wattage	Lamp type	Options
EF40= Die-cast back plate single head	(LA)= 6V-4W, MR16 LED	Blank= White	Blank= No options
EF40D = Die-cast back plate double head	(LB)= 6V-5W, MR16 LED	-BK= Black	T= Tamper proof
	(LG)= 12V-4W, MR16 LED	-GY = Gray	screws
	(LI)= 12V-5W, MR16 LED	-	
	(LJ)= 12V-6W, MR16 LED		
	(LL)= 24V-4W, MR16 LED		
Example: EF40D(LJ)			