Survive-All[™] EF41 Series

Class I division II certified remote fixture



Description

- Available with single or double lamp heads
- Die-cast aluminum back plate with gasket
- Vandal-resistant UV stabilized polycarbonate lamp cover
- Comes standard with tamper-proof screws and bit
- Universal J-box mounting
- Extreme operational temperature range: -40°F to +104°F (-40°C to +40°C)

Mounting

- Surface mount
- Conduit entry 1/2" NPT

Approval

- CSA-US (To UL 924 standards)
- Evaluated to the UL 844 Standard for Class I Division 2, Groups A, B, C and D


Warranty

· Unit has a five-year limited warranty Detailed warranty terms located on page 178 or onli www.emergi-lite.com/usa/files/EL_Warranty.pdf

nl	in	ea	at:	
		(શ	2


Photometric performance


	Spacing center-to-center (feet)		
Lamp	7' mounting height	15' mounting height	
LA	39'	34'	
LB	74'	57'	
LG	49'	39'	
LI	68'	54'	
LJ	89'	80'	
LL	51'	39'	
LW	43'	39'	



Dimensions

Dimensions are approximate and subject to change.





Lamp selection chart and temperature code

Lamp				Replacement	Temp.	Max.
suffix	Voltage	Wattage	Lumens	number	code	temp.
LA	6	4	200	580.0097-E	T4A	120°C
LB	6	5	415	580.0122-E	T4A	120°C
LG	12	4	220	580.0093-E	Т5	100°C
LI	12	5	340	580.0104-E	T4A	120°C
LJ	12	6	540	580.0106-E	T4	135°C
LL	24	4	220	580.0098-E	Т5	100°C
LW	120	4	230	580.0113-E	T4A	120°C

How to order

Series	Lamp ty	pe/ wattage	Color	
EF41= Single	(LA)= 6\	/-4W, MR16 LED	-GY= Gray	
lamp	(LB)= 6V	/-5W, MR16 LED		
EF41D= Double	(LG)= 12V-4W, MR16 LED			
lamp	(LI)= 12	V-5W, MR16 LED		
	(LJ)= 12V-6W, MR16 LED			
	(LL)= 24V-4W, MR16 LED			
	(LW)= 12	20V-4W, MR16 LED (C/W wires	5)	
Example: EF41	(MJ)-GY			

¹Wattage doubles for "D" 2-lamp version

115