EXC LED Series

Class I, Division 1 & 2, Group C & D; Class II, Division 1 & 2, Group E, F & G; Class III remote fixture for hazardous locations



Housing

- One-piece heavy gauge, corrosion resistant, copper-free cast aluminum
- Consists of a housing with provisions for up to two lighting heads
- Spin-off gasketed cover prevents propagation of internally generated arcs
- Stainless steel vent/drain
- Lighting head fixtures are heavy cast aluminum with Pyrex® lens
- Exit faceplate: heavy-duty 20 gauge steel, baked enamel gray finish
- 6 inch EXIT lettering legend, available in red or green
- Field-selectable chevrons

Mounting

- Surface wall mount
- 3/4" NPT conduit entry on top and bottom of housing
- Single and double pendant mount heads include elbow swivel, conduit extension pipe (6" increments)

Electronics

- · Pulse plus charger
- Low voltage disconnect
- · Automatic brownout protection
- · Battery lock-out
- Fused output circuit
- 120/277 60Hz

Lamp type

- · Heads offer a choice of MR16 LED lamp wattages
- Exit sign uses a 3 watt LED lamp

Battery type

• 6V or 12V, nickel-cadmium battery

Approvals

- CSA-US (to UL 924 standards)
- Manufactured in accordance with UL844, UL1203
- Class I, Division 1 & 2, Groups C & D
- Class II, Division 1 & 2, Groups E, F & G
- Class III
- NEC, OSHA and NEMA compliant for above Classes and Groups
- Temperature code T6




Warranty

Unit has five-year warranty
 Detailed warranty terms located on page 178 or
 online at: www.emergi-lite.com/usa/files/EL_Warranty.pdf


Photometric performance

	Spacing center-to-center (feet)			
Lamp	7' mounting height	15' mounting height		
2 x LA	43'	29'		
2 x LB	70'	39'		
2 x LG	55'	36'		
2 x LI	67'	41'		
2 x LJ	87'	62'		



Dimensions

Dimensions are approximate and subject to change.



Housing:

12" X 12" X 9 1/2"

(4) Mounting Lugs:

10" and 13- 1/2" on center

Overall dimensions (including fixtures): 38" X 38" X 10"

Standard configurations for EXC Series

Unit	Catalog number examples	Description
	6EXC1	6 volt self contained hazardous location emergency battery unit 18 watts of remote capacity.
(Remote capability)	6EXC1-TS	6 volt self contained hazardous location emergency battery unit 18 watts of remote capacity. Transfer switch included for use with remote exit signs (maximum 5 exit signs per TS).
	12EXC4-1LI	12 volt self contained hazardous location emergency battery unit with one head containing 2 X 12V 5W MR16 LED lamps, 30 watts of remote capacity.
		12 volt self contained hazardous location emergency battery unit with one head containing 2 X 12V 5W MR16 LED lamps, 30 watts of remote capacity. Transfer switch included for use with remote exit signs (maximum 5 exit signs per TS).
	12EXC4-1LI-TS	
	6EXC3-2LA	6 volt self contained hazardous location emergency battery unit with two heads, each containing 2 X 6V 4W MR16 LED lamps, 14 watts of remote.
	6EXC3-2LA-TS	6 volt self contained hazardous location emergency battery unit with two heads, each containing 2 X 6V 4W MR16 LED lamps, 14 watts of remote capacity. Transfer switch included for use with remote exit signs (maximum 5 exit signs per TS).
EXIT	6EXC1-TS-T1LR	6 volt self contained exit sign with 15 watts of remote capacity. Transfer switch included for use with integral exit sign and additional remote exit signs (maximum 5 exit signs per TS).
EXIT	12EXC4-1LJ-TS-T1LR	12 volt self contained combination unit with 25 watts of remote capacity. Transfer switch included for use with integral exit sign and additional remote exit signs (maximum 5 exit signs per TS).

Note: Exit signs utilise a 3 watt bayonnet base LED bulb fabricated at our North American facility.

Unit rating – equipment with remote capability

Sealed maintenance-			Battery capacity in w			
free battery type	D.C. voltage Model number		1-1/2 hrs	2 hrs	4 hrs	8 hrs
Nickel-cadmium -	6	EXC1	8	12	9	6
	6	EXC3	30	20	15	10
	12	EXC2	24	18	12	9
	12	EXC4	40	30	20	15

How to order

Series / capacity		# of heads and lamps	Lamp wattage/type	Battery unit option	
6EXC1= 6Vdc battery unit/combo 18 6EXC3= 6Vdc battery unit/combo 30 12EXC2= 12Vdc battery unit/combo 12EXC4= 12Vdc battery unit/combo	OW (6V only) 24W (12V only)	-0= No emergency head -1= Single head, two lamps -2= Two heads, two lamps each	LA= 6V 4W MR16 LED LB= 6V 5W MR16 LED LG= 12V 4W MR16 LED LI= 12V 5W MR16 LED LJ= 12V 6W MR16 LED	Blank= No transfer panel -TS= Transfer panel (required to supply remote exit sign only)	
Exit sign # of faces	Exit sign lamp		Exit sign letter color		
Blank= No exit sign -T1= Single face exit sign	L= LED exit sign		Blank= No exit sign R= Red		
Example: 12EXC4-1LJ-TS-T1LR			G = Green		