# Survive-All™ SVX Series

NEMA-4X, vandal resistant and harsh environment exit sign
















#### Construction

- Full gasketed NEMA-4X housing
- · Frame: polyvinyl chloride enclosure, fully gasketed around the lens, backplate and canopy to prevent water infiltration
- Faceplate: heavy-duty, vandal-resistant polycarbonate
- · Backplate: heavy aluminum
- · Comes with both Phillips head for NSF location and tamper-proof screws
- 6 inch EXIT lettering legend, available in red or green
- · Field-selectable chevrons
- · Choice of finishes: black, white, gray or brushed aluminum

#### Mounting

- · Surface mount
- · Ceiling and wall mount are NEMA-4X
- End and pendant mount are not NEMA-4X
- · Canopy included for end or ceiling mount applications
- · Universal J-box mounting
- 1/2 inch conduit entry on top and sides

### Special wording panels

· Available. Contact your sales representative with your design requirements

#### **Electronics**

- · Magnetically operated test switch
- Standard Advanced Diagnostics (non-audible)
- Optional Nexus®Pro IoT monitoring system
- Optional Nexus® wireless monitoring system
- 120/277 60Hz
- Compatible with Emergi-Lite mini-inverters (contact your sales representative for more information)

### **Approvals**

- UL 924 listed
- UL listed for wet and damp location self powered (50°F to 104°F), AC and AC/DC (-40°F to 104°F)
- Self powered model UL listed for cold weather option (-4°F to +104°F)
- Meets NFPA101 (Life Safety Code), NFPA 70 NEC, OSHA illumination standards
- E-California Energy Commission Title 20

#### Warranty

• Five-year limited warranty Detailed warranty terms located on page 202 or online at: www.emergi-lite.com/usa/files/EL\_Warranty.pdf

## Power consumption

Model	AC specs	DC specs	
AC-only	120-277VAC,		
	50/60Hz (1.2W)	_	
AC/DC	120-277VAC,	6 to 24VDC	
	50/60Hz (1.2W)	(less than 1.5W)	
Self-powered	120-277VAC,	Ni-Cd battery	
	50/60Hz (3.7W)	(min. 90 minutes)	

#### **Housing color**










Brushed aluminum

#### **Dimensions**

Dimensions are approximate and subject to change.



Accessories (order as a separate item)

Description	Part number
Tamper-proof bit	690.0454-E
Convert single to double face, red	DFKR <sup>1</sup>
Convert single face to double face, green	DFKG <sup>1</sup>
Additional test magnet	199.0133-E

<sup>&</sup>lt;sup>1</sup>Colors available AL-BK-WT

## How to order

Housing color	Series	Face	Legend	Charger type
BB= Black/black	SVX= AC only	1= Single	R= Red	Blank= AC only
<b>BW</b> = Black/white	SVXN= Self- powered Ni-Cd	2= Double	<b>G</b> = Green	-D= Diagnostic¹
BA= Black/aluminum				-NEXP= Nexus®Pro IoT1
GB= Gray/black				-NEXRF= Nexus® wireless1
<b>GW</b> = Gray/white				
GA= Gray/aluminum				
<b>WB</b> = White/black				
<b>WW</b> = White/white				
WA= White/aluminum		Housing	Options	
		-4X= Wet/damp	<u> </u>	o options
		locations		Pual circuit (AC only) <sup>2</sup>
				d weather (Self-powered -4°F to 104°F)4
				nopy pendant mount⁵
			<b>-DC</b> = 6 to	
			-FA= Fire	alarm activated flasher <sup>2</sup>
			-FL= Flas	her only <sup>2</sup>
			<b>-FZ</b> = Flas	her/buzzer (self-powered only) <sup>2</sup>
Example: BBSVXN1R-D-4X-FA				

<sup>&</sup>lt;sup>1</sup>Available with self-powered models only

<sup>&</sup>lt;sup>2</sup>Not available with Nexus® option <sup>3</sup>Not available with self-power

<sup>&</sup>lt;sup>4</sup>Not required with AC model