



OL-24/LED/DZ

Slave 2 watt, 24 Volt surface mount led luminaire, series Optilux

Product Information

Type	OL-24/LED/DZ
Catalog number	11112099
Category_	Escape route signalisation
GTIN	08713812746500
GID	7TCA091130R0001
Serie	Optilux
Warranty (Year)	5
Other	The luminaire is equipped with a light dimming circuit, the minimum output is in accordance with the standard



Characteristics

Power supply system	Central
Continuous operation	Yes
Mounting Method	Ceiling
Mounting form	Surface
Material housing	Aluminium / plastic
Colour housing	White / aluminium
Material cover	Other
Material	Aluminium / polycarbonate
Colour	White / aluminium
Length (mm)	364
Width (mm)	167
Height/depth (mm)	82
Nominal voltage (V)	24
Voltage type	AC/DC
Monitoring equipment	None
With lamp	Yes
Lamp Type	Led
Lamp holder	Other
Lamp power (W)	2
Number of lamps	1
Average lifespan light source (hours)	100.000
Colour of light	White
Colour temperature (K)	6350
CRI	60
Protection class	I
Degree of protection (IP)	40
With remote switch connection	No
Wiring system	Maintained / non-maintained circuit
Type of indicator	Single / double-sided
Labelling type	Acrylic plate
Recognition distance (m)	25
Circuit	Other
Inrush Current (A - 0.1ms)	7 / 4,5
Powerfactor	0,65
Temperature range (°C)	0 ~ +35

Article Details

Product class	Emergency luminaire
---------------	---------------------

E-code	EC001957
Discount group	30405
Harmonized code	9405408440
GLN	8713812000008

Ordering information

Orderable	Yes
Order-Unit	Pieces
Minimum order quantity	1
Order Increment	1

Supply Information

Weight (kg)	1,121
Packaging	Cardboard box
Packaging dimensions (LxWxH) (mm)	426 x 188 x 111