

NMTR.E175441 - Power Circuit and Motor-mounted Apparatus

Note: We are enhancing our systems and you may notice duplicate entries/missing/outdated data. During this interim period, please contact our Customer Service at <https://www.ul.com/about/locations>.

Power Circuit and Motor-mounted Apparatus

ABB AB, Control Products

E175441

Motorgrand 20

Vasteras, SE-721 61 Sweden

Acoustic elements, Model(s): [1SFA616073R1104](#), [1SFA616073R1104](#), [1SFA616073R1204](#), [1SFA616073R1204](#), [1SFA616073R2004](#), [1SFA616073R2004](#), [1SFA616073R3004](#), [1SFA616073R3004](#)

Buzzers, Model(s): [1SFA 615080R1134](#), [1SFA 615080R1134](#), [1SFA 616080R1131](#), [1SFA 616080R1131](#), [1SFA 616080R1132](#), [1SFA 616080R1132](#), [1SFA 616080R1133](#), [1SFA 616080R1133](#), [1SFA 616080R1138](#), [1SFA 616080R1138](#), [1SFA 616080R1231](#), [1SFA 616080R1231](#), [1SFA 616080R1232](#), [1SFA 616080R1232](#), [1SFA 616080R1233](#), [1SFA 616080R1233](#), [1SFA 616080R1234](#), [1SFA 616080R1234](#), [1SFA 616080R1238](#), [1SFA 616080R1238](#), [1SFA 616080R2031](#), [1SFA 616080R2031](#), [1SFA 616080R2032](#), [1SFA 616080R2032](#), [1SFA 616080R2033](#), [1SFA 616080R2033](#), [1SFA 616080R2034](#), [1SFA 616080R2034](#), [1SFA 616080R2038](#), [1SFA 616080R2038](#), [1SFA 616080R3051](#), [1SFA 616080R3051](#), [1SFA 616080R3052](#), [1SFA 616080R3052](#), [1SFA 616080R3053](#), [1SFA 616080R3053](#), [1SFA 616080R3062](#), [1SFA 616080R3062](#), [1SFA 616080R3063](#), [1SFA 616080R3063](#), [1SFA 616080R3071](#), [1SFA 616080R3071](#), [1SFA 616080R3072](#), [1SFA 616080R3072](#), [1SFA 616080R3073](#), [1SFA 616080R3073](#), [1SFA 616080R4011](#), [1SFA 616080R4011](#), [1SFA 616080R4012](#), [1SFA 616080R4012](#), [1SFA 616080R4013](#), [1SFA 616080R4013](#), [1SFA 616080R4014](#), [1SFA 616080R4014](#), [1SFA 616080R4018](#), [1SFA 616080R4018](#), [1SFA 616401R4010](#), [1SFA 616401R4010](#), [1SFA 616401R4030](#), [1SFA 616401R4030](#), [1SFA 616401R4040](#), [1SFA 616401R4040](#), [1SFA 616401R4110](#), [1SFA 616401R4110](#), [1SFA 616401R4130](#), [1SFA 616401R4130](#), [1SFA 616401R4140](#), [1SFA 616401R4140](#), [1SFA 616808R3061](#), [1SFA 616808R3061](#)

Signal light accessories, Model(s): [1SFA 616077R1011](#), [1SFA 616077R1011](#), [1SFA 616077R1012](#), [1SFA 616077R1012](#), [1SFA 616077R1021](#), [1SFA 616077R1021](#), [1SFA 616077R1022](#), [1SFA 616077R1022](#), [1SFA 616077R1031](#), [1SFA 616077R1031](#), [1SFA 616077R1032](#), [1SFA 616077R1032](#), [1SFA616070R3054](#), [1SFA616070R3054](#), [1SFA616070R3058](#), [1SFA616070R3058](#), [1SFA616070R3064](#), [1SFA616070R3064](#), [1SFA616070R3068](#), [1SFA616070R3068](#), [1SFA616070R3074](#), [1SFA616070R3074](#), [1SFA616070R3078](#), [1SFA616070R3078](#)

Signal lights, Model(s): [1SFA 616050R1121](#), [1SFA 616050R1121](#), [1SFA 616050R1122](#), [1SFA 616050R1122](#), [1SFA 616050R1123](#), [1SFA 616050R1123](#), [1SFA 616050R1124](#), [1SFA 616050R1124](#), [1SFA 616050R1128](#), [1SFA 616050R1128](#), [1SFA 616050R1222](#), [1SFA 616050R1222](#), [1SFA 616050R1223](#), [1SFA 616050R1223](#), [1SFA 616050R1224](#), [1SFA 616050R1224](#), [1SFA 616050R1228](#), [1SFA 616050R1228](#), [1SFA 616050R3021](#), [1SFA 616050R3021](#), [1SFA 616050R3022](#), [1SFA 616050R3022](#), [1SFA 616050R3023](#), [1SFA 616050R3023](#), [1SFA 616050R3024](#), [1SFA 616050R3024](#), [1SFA 616050R3028](#), [1SFA 616050R3028](#), [1SFA 616050R3051](#), [1SFA 616050R3051](#), [1SFA 616050R3052](#), [1SFA 616050R3052](#), [1SFA 616050R3053](#), [1SFA 616050R3053](#), [1SFA 616050R4011](#), [1SFA 616050R4011](#), [1SFA 616050R4012](#), [1SFA 616050R4012](#), [1SFA 616050R4013](#), [1SFA 616050R4013](#), [1SFA 616050R4014](#), [1SFA 616050R4014](#), [1SFA 616050R4018](#), [1SFA 616050R4018](#), [1SFA 616051R3001](#), [1SFA 616051R3001](#), [1SFA 616051R3101](#), [1SFA 616051R3101](#), [1SFA 616070E3063](#), [1SFA 616070E3063](#), [1SFA 616070R1131](#), [1SFA 616070R1131](#), [1SFA 616070R1132](#), [1SFA 616070R1132](#), [1SFA 616070R1133](#), [1SFA 616070R1133](#), [1SFA 616070R1134](#), [1SFA 616070R1134](#), [1SFA 616070R1138](#), [1SFA 616070R1138](#), [1SFA 616070R1231](#), [1SFA 616070R1231](#), [1SFA 616070R1232](#), [1SFA 616070R1232](#), [1SFA 616070R1233](#), [1SFA 616070R1233](#), [1SFA 616070R1234](#), [1SFA 616070R1234](#), [1SFA 616070R1238](#), [1SFA 616070R1238](#), [1SFA 616070R2031](#), [1SFA 616070R2031](#), [1SFA 616070R2032](#), [1SFA 616070R2032](#), [1SFA 616070R2033](#), [1SFA 616070R2033](#), [1SFA 616070R2034](#), [1SFA 616070R2034](#), [1SFA 616070R2038](#), [1SFA 616070R2038](#), [1SFA 616070R3021](#), [1SFA 616070R3021](#), [1SFA 616070R3022](#), [1SFA 616070R3022](#), [1SFA 616070R3023](#), [1SFA 616070R3023](#), [1SFA 616070R3024](#), [1SFA 616070R3024](#), [1SFA 616070R3051](#), [1SFA 616070R3051](#), [1SFA 616070R3052](#), [1SFA 616070R3052](#), [1SFA 616070R3053](#), [1SFA 616070R3053](#), [1SFA 616070R3061](#), [1SFA 616070R3061](#), [1SFA 616070R3062](#), [1SFA 616070R3062](#), [1SFA 616070R3071](#), [1SFA 616070R3071](#), [1SFA 616070R3072](#), [1SFA 616070R3072](#), [1SFA 616070R3073](#), [1SFA 616070R3073](#), [1SFA 616070R3121](#), [1SFA 616070R3121](#), [1SFA 616070R3122](#), [1SFA 616070R3122](#)

[616070R3122](#), [1SFA 616070R3123](#), [1SFA 616070R3123](#), [1SFA 616070R3124](#), [1SFA 616070R3124](#), [1SFA 616070R3128](#), [1SFA 616070R3128](#), [1SFA 616070R3221](#), [1SFA 616070R3221](#), [1SFA 616070R3222](#), [1SFA 616070R3222](#), [1SFA 616070R3223](#), [1SFA 616070R3223](#), [1SFA 616070R3224](#), [1SFA 616070R3224](#), [1SFA 616070R3228](#), [1SFA 616070R3228](#), [1SFA 616070R4011](#), [1SFA 616070R4011](#), [1SFA 616070R4012](#), [1SFA 616070R4012](#), [1SFA 616070R4013](#), [1SFA 616070R4013](#), [1SFA 616070R4014](#), [1SFA 616070R4014](#), [1SFA 616070R4018](#), [1SFA 616070R4018](#), [1SFA 616071R1201](#), [1SFA 616071R1201](#), [1SFA 616071R3001](#), [1SFA 616071R3001](#), [1SFA 616071R3101](#), [1SFA 616071R3101](#), [1SFA 616079R4101](#), [1SFA 616079R4101](#), [1SFA 626051R1201](#), [1SFA 626051R1201](#), [1SFA616070R3421](#), [1SFA616070R3421](#), [1SFA616070R3422](#), [1SFA616070R3422](#), [1SFA616070R3423](#), [1SFA616070R3423](#), [1SFA616070R3424](#), [1SFA616070R3424](#), [1SFA616070R3428](#), [1SFA616070R3428](#), [1SFA616070R3521](#), [1SFA616070R3521](#), [1SFA616070R3522](#), [1SFA616070R3522](#), [1SFA616070R3523](#), [1SFA616070R3523](#), [1SFA616070R3524](#), [1SFA616070R3524](#), [1SFA616070R3528](#), [1SFA616070R3528](#), [1SFA616080R1151](#), [1SFA616080R1151](#), [1SFA616080R1152](#), [1SFA616080R1152](#), [1SFA616080R1153](#), [1SFA616080R1153](#)

Terminal Module, Model(s): [1SFA 616055R1001](#), [1SFA 616055R1001](#), [1SFA 616075R1001](#), [1SFA 616075R1001](#), [1SFA 616075R1002](#), [1SFA 616075R1002](#), [1SFA 626051R1201](#), [1SFA 626051R1201](#)

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2021 UL LLC"