



EVA-DIP-22/CIS

Self-contained 2 watt, aluminium maintained recess 22 meter led luminaire, including control module, series Evago. The luminaire is including the pictogram PP 220/51 (escape route straight forward) + green pictogram (PP 220/50)

Product Information

EVA-DIP-22/CIS Type Catalog number 4510216162

Category_ Escape route signalisation

GTIN 08713812760650 GID 7TCA091180R0171

Serie Evago Warranty (Year) 5

Other The luminaire is equipped with a light

> dimming circuit, the minimum output is in accordance with the standard. Including round and square decorative

covers









Characteristics

Power supply system Self-contained individual battery

Continuous operation Yes Mounting Method Ceiling Mounting form Recess

Material housing Aluminium / plastic

Colour housing Aluminium

Material Aluminium / polycarbonate

Colour Aluminium Length (mm) 235 Width (mm) 84 Height/depth (mm) 134 Maximum outer diameter (mm) 84 Built-in length (mm) 300 Built-in width (mm) 68 Built-in diameter (mm) 68 Built-in depth (mm) 48 Nominal voltage (V) 230 Voltage type AC Duration (hours) **Battery** NiMH

Monitoring equipment Safety module for monitoring

With lamp Yes Lamp Type Led Lamp holder Other Lamp power (W) 2 Number of lamps 1

Average lifespan light source (hours) 100.000 Colour of light White Colour temperature (K) 5000 CRI 80 Protection class Ш Degree of protection (IP) 40 With remote switch connection No

Wiring system Maintained / non-maintained circuit Type of indicator Single / double-sided Labelling type Insert sheet/plate

Recognition distance (m) 22
Circuit Other
Power consumption maintained mode (W) 4

Apparent power consumption maintained mode (VA) 4,4

Nominal current (mA) 19 Powerfactor > 0,9 Temperature range (°C) $5 \sim +35$

Article Details

Product class Emergency luminaire

 E-code
 EC001957

 Discount group
 30502

 Harmonized code
 9405408440

 GLN
 8713812000008

Ordering information

Order-Unit Pieces
Minimum order quantity 1
Order Increment 1

Supply Information

Weight (kg) 0,919

Packaging Cardboard box
Packaging dimensions (LxWxH) (mm) 300 x 205 x 88