



IL-230HF/LED/DZ/FLX

Slave 2 watt, 230 Volt recess led luminaire, including control module, series Optilux

Product Information

Type	IL-230HF/LED/DZ/FLX
Catalog number	11112102-005
Category_	Escape route signalisation
GTIN	08713812759388
GID	7TCA091140R0288
Serie	Optilux
Warranty (Year)	5



Characteristics

Power supply system	Central
Continuous operation	Yes
Mounting Method	Ceiling
Mounting form	Recess
Material housing	Zendimir galvanized steel / plastic
Colour housing	White
Material cover	Other
Material	Steel / polycarbonate
Colour	White / aluminium
Length (mm)	364
Width (mm)	167
Height/depth (mm)	89
Built-in length (mm)	292
Built-in width (mm)	120
Built-in depth (mm)	43
Nominal voltage (V)	230
Voltage type	DC
Monitoring equipment	Safety module for monitoring
With lamp	Yes
Lamp Type	Led
Lamp holder	Other
Lamp power (W)	2
Number of lamps	1
Average lifespan light source (hours)	100.000
Colour of light	White
Colour temperature (K)	6350
CRI	60
Protection class	I
Degree of protection (IP)	20
With remote switch connection	No
Wiring system	Maintained / non-maintained circuit
Type of indicator	Single / double-sided
Labelling type	Acrylic plate
Recognition distance (m)	25
Circuit	Other
Power consumption maintained mode (W)	3,5
Apparent power consumption maintained mode (VA)	8
Nominal current (mA)	29,6
Inrush Current (A - 0.1ms)	27
Powerfactor	0,45

Temperature range (°C)	5 ~ +25
Article Details	
Product class	Emergency luminaire
E-code	EC001957
Discount group	30406
Harmonized code	9405408440
GLN	8713812000008
Ordering information	
Orderable	Yes
Order-Unit	Pieces
Minimum order quantity	1
Order Increment	1
Supply Information	
Weight (kg)	1,641
Packaging	Cardboard box
Packaging dimensions (LxWxH) (mm)	426 x 188 x 111