



ILN-3/CIS/LED/DZ

Self-contained 3 hours 2 watt, maintained recess led luminaire, including control module, series Optilux

Product Information

Type	ILN-3/CIS/LED/DZ
Catalog number	11112117-002
Category_	Escape route signalisation
GTIN	08713812746975
GID	7TCA091180R0008
Serie	Optilux
Warranty (Year)	5
Other	The luminaire is equipped with a light dimming circuit, the minimum output is in accordance with the standard



Characteristics

Power supply system	Self-contained individual battery
Continuous operation	Yes
Mounting Method	Ceiling
Mounting form	Recess
Material housing	Zendzimir galvanized steel / plastic
Colour housing	White
Material cover	Other
Material	Steel / polycarbonate
Colour	White / aluminium
Length (mm)	364
Width (mm)	167
Height/depth (mm)	89
Built-in length (mm)	292
Built-in width (mm)	120
Built-in depth (mm)	43
Nominal voltage (V)	230
Voltage type	AC
Duration (hours)	3
Battery	NiCd
Monitoring equipment	Safety module for monitoring
With lamp	Yes
Lamp Type	Led
Lamp holder	Other
Lamp power (W)	2
Number of lamps	1
Average lifespan light source (hours)	100.000
Colour of light	White
Colour temperature (K)	6350
CRI	60
Protection class	I
Degree of protection (IP)	20
With remote switch connection	No
Wiring system	Maintained / non-maintained circuit
Type of indicator	Single / double-sided
Labelling type	Acrylic plate
Recognition distance (m)	25
Circuit	Other

Power consumption maintained mode (W)	5,1
Apparent power consumption maintained mode (VA)	9,9
Nominal current (mA)	42,5
Inrush Current (A - 0.1ms)	18
Powerfactor	0,52
Temperature range (°C)	0 ~ +35

Article Details

Product class	Emergency luminaire
E-code	EC001957
Discount group	30502
Harmonized code	9405408440
GLN	8713812000008

Ordering information

Orderable	Yes
Order-Unit	Pieces
Minimum order quantity	1
Order Increment	1

Supply Information

Weight (kg)	1,084
Packaging	Cardboard box
Packaging dimensions (LxWxH) (mm)	426 x 188 x 111