



OLN-1/ZT/LED/DZ

Self-contained 2 watt, maintained surface mount led luminaire, including automatic self test, series Optilux

Product Information

Type	OLN-1/ZT/LED/DZ
Catalog number	11112116
Category_	Escape route signalisation
GTIN	08713812745435
GID	7TCA091160R0006
Serie	Optilux
Warranty (Year)	5
Other	The luminaire is equipped with a light dimming circuit, the minimum output is in accordance with the standard



Characteristics

Power supply system	Self-contained individual battery
Continuous operation	Yes
Mounting Method	Ceiling
Mounting form	Surface
Material housing	Aluminium / plastic
Colour housing	White / aluminium
Material cover	Other
Material	Aluminium / polycarbonate
Colour	White / aluminium
Length (mm)	364
Width (mm)	167
Height/depth (mm)	82
Nominal voltage (V)	230
Voltage type	AC
Duration (hours)	1
Battery	NiCd
Monitoring equipment	Automatic self test
With lamp	Yes
Lamp Type	Led
Lamp holder	Other
Lamp power (W)	2
Number of lamps	1
Average lifespan light source (hours)	100.000
Colour of light	White
Colour temperature (K)	6350
CRI	60
Protection class	I
Degree of protection (IP)	40
With remote switch connection	No
Wiring system	Maintained / non-maintained circuit
Type of indicator	Single / double-sided
Labelling type	Acrylic plate
Recognition distance (m)	25
Circuit	Other
Power consumption maintained mode (W)	5,1
Apparent power consumption maintained mode (VA)	9,9

Nominal current (mA)	42,5
Inrush Current (A - 0.1ms)	18
Powerfactor	0,52
Temperature range (°C)	0 ~ +35

Article Details

Product class	Emergency luminaire
E-code	EC001957
Discount group	30901
Harmonized code	9405409100
GLN	8713812000008

Ordering information

Orderable	Yes
Order-Unit	Pieces
Minimum order quantity	1
Order Increment	1

Supply Information

Weight (kg)	1,297
Packaging	Cardboard box
Packaging dimensions (LxWxH) (mm)	426 x 188 x 111