



HIL-DLO/CIS

Self-contained 7 watt maintained surface mount led luminaire, including control module, series Hiled. Light distribution: long (L), RAL9003 + RAL7015

Product Information

Type	HIL-DLO/CIS
Catalog number	11170042
Category_	Escape route lighting
GTIN	05415022425437
GID	7TCA091720R0094
Serie	Hiled
Warranty (Year)	5



Characteristics

Power supply system	Self-contained individual battery
Continuous operation	Yes
Mounting Method	Ceiling;Wall
Mounting form	Surface
Material housing	Aluminium / plastic
Colour housing	White
Material	Aluminium / polycarbonate
Colour	White
Length (mm)	326
Width (mm)	143
Height/depth (mm)	109
Nominal voltage (V)	230
Voltage type	AC
Duration (hours)	1
Battery	NiCd
Monitoring equipment	Safety module for monitoring
With lamp	Yes
Lamp Type	Led
Lamp holder	Other
Lamp power (W)	7
Number of lamps	1
Light output in emergency operation (lm)	1000
Average lifespan light source (hours)	60.000
Colour of light	White
Colour temperature (K)	6200
CRI	68
Protection class	II
Degree of protection (IP)	65
With remote switch connection	No
Wiring system	Maintained / non-maintained circuit
Type of indicator	Not applicable
Circuit	Other
Impact strength (IK)	08
Power consumption maintained mode (W)	8 / 3
Apparent power consumption maintained mode (VA)	9 / 5
Temperature range (°C)	0 ~ +40

Article Details

Product class	Emergency luminaire
---------------	---------------------

E-code	EC001957
Discount group	30901
Harmonized code	9405606000
GLN	8713812000008

Ordering information

Orderable	Yes
Order-Unit	Pieces
Minimum order quantity	1
Order Increment	1

Supply Information

Weight (kg)	2,300
Packaging	Cardboard box
Packaging dimensions (LxWxH) (mm)	436 x 215 x 146