



## PRE-HF/LED

Slave 1 watt, 230 Volt surface mount led luminaire, series Previs. the luminaire is including the pictogram escape route straight forward (P51-PRE).

### Product Information

|                 |                                                                                                               |
|-----------------|---------------------------------------------------------------------------------------------------------------|
| Type            | PRE-HF/LED                                                                                                    |
| Catalog number  | 14062021                                                                                                      |
| Category_       | Escape route signalisation                                                                                    |
| GTIN            | 08713812749655                                                                                                |
| GID             | 7TCA091130R0025                                                                                               |
| Serie           | Previs                                                                                                        |
| Warranty (Year) | 5                                                                                                             |
| Other           | The luminaire is equipped with a light dimming circuit, the minimum output is in accordance with the standard |



### Characteristics

|                                                 |                                     |
|-------------------------------------------------|-------------------------------------|
| Power supply system                             | Central                             |
| Continuous operation                            | Yes                                 |
| Mounting Method                                 | Wall                                |
| Mounting form                                   | Surface                             |
| Material housing                                | Plastic                             |
| Colour housing                                  | White                               |
| Material cover                                  | Plastic, transparent                |
| Material                                        | Polycarbonate                       |
| Colour                                          | White                               |
| Length (mm)                                     | 287                                 |
| Width (mm)                                      | 136                                 |
| Height/depth (mm)                               | 67                                  |
| Nominal voltage (V)                             | 230                                 |
| Voltage type                                    | AC/DC                               |
| Monitoring equipment                            | None                                |
| With lamp                                       | Yes                                 |
| Lamp Type                                       | Led                                 |
| Lamp holder                                     | Other                               |
| Lamp power (W)                                  | 1                                   |
| Number of lamps                                 | 2                                   |
| Average lifespan light source (hours)           | 100.000                             |
| Colour of light                                 | White                               |
| Colour temperature (K)                          | 6350                                |
| CRI                                             | 73                                  |
| Protection class                                | II                                  |
| Degree of protection (IP)                       | 40                                  |
| With remote switch connection                   | No                                  |
| Wiring system                                   | Maintained / non-maintained circuit |
| Type of indicator                               | Single / double-sided               |
| Labelling type                                  | Insert sheet/plate                  |
| Recognition distance (m)                        | 25                                  |
| Circuit                                         | Other                               |
| Power consumption maintained mode (W)           | 3,8                                 |
| Apparent power consumption maintained mode (VA) | 7,7                                 |
| Nominal current (mA)                            | 33,5                                |
| Inrush Current (A - 0.1ms)                      | 22,5                                |

|                        |         |
|------------------------|---------|
| Powerfactor            | 0,49    |
| Temperature range (°C) | 0 ~ +35 |

#### Article Details

|                 |                     |
|-----------------|---------------------|
| Product class   | Emergency luminaire |
| E-code          | EC001957            |
| Discount group  | 30405               |
| Harmonized code | 9405408440          |
| GLN             | 8713812000008       |

#### Ordering information

|                        |        |
|------------------------|--------|
| Orderable              | Yes    |
| Order-Unit             | Pieces |
| Minimum order quantity | 1      |
| Order Increment        | 1      |

#### Supply Information

|                                   |                |
|-----------------------------------|----------------|
| Weight (kg)                       | 0,766          |
| Packaging                         | Cardboard box  |
| Packaging dimensions (LxWxH) (mm) | 300 x 150 x 95 |