



## PRE-HF/V/LED

Slave 2 watt, 230 Volt surface mount led luminaire, series Previx

### Product Information

|                 |                       |
|-----------------|-----------------------|
| Type            | PRE-HF/V/LED          |
| Catalog number  | 14063021              |
| Category_       | Escape route lighting |
| GTIN            | 08713812755311        |
| GID             | 7TCA091130R0295       |
| Serie           | Previx                |
| Warranty (Year) | 5                     |



### Characteristics

|                                                 |                                     |
|-------------------------------------------------|-------------------------------------|
| Power supply system                             | Central                             |
| Continuous operation                            | Yes                                 |
| Mounting Method                                 | Ceiling                             |
| Mounting form                                   | Surface                             |
| Material housing                                | Plastic                             |
| Colour housing                                  | White                               |
| Material cover                                  | Plastic, transparent                |
| Material                                        | Polycarbonate                       |
| Colour                                          | White                               |
| Length (mm)                                     | 287                                 |
| Width (mm)                                      | 136                                 |
| Height/depth (mm)                               | 67                                  |
| Nominal voltage (V)                             | 230                                 |
| Voltage type                                    | AC/DC                               |
| Monitoring equipment                            | None                                |
| With lamp                                       | Yes                                 |
| Lamp Type                                       | Led                                 |
| Lamp holder                                     | Other                               |
| Lamp power (W)                                  | 2                                   |
| Number of lamps                                 | 1                                   |
| Light output in emergency operation (lm)        | 107                                 |
| Average lifespan light source (hours)           | 100.000                             |
| Colour of light                                 | White                               |
| CRI                                             | 60                                  |
| Protection class                                | II                                  |
| Degree of protection (IP)                       | 40                                  |
| With remote switch connection                   | No                                  |
| Wiring system                                   | Maintained / non-maintained circuit |
| Type of indicator                               | Not applicable                      |
| Circuit                                         | Other                               |
| Power consumption maintained mode (W)           | 3,8                                 |
| Apparent power consumption maintained mode (VA) | 7,7                                 |
| Nominal current (mA)                            | 33,5                                |
| Inrush Current (A - 0.1ms)                      | 22,5                                |
| Powerfactor                                     | 0,49                                |
| Temperature range (°C)                          | 0 ~ +35                             |

### Article Details

|               |                     |
|---------------|---------------------|
| Product class | Emergency luminaire |
| E-code        | EC001957            |

|                 |               |
|-----------------|---------------|
| Discount group  | 30405         |
| Harmonized code | 9405408440    |
| GLN             | 8713812000008 |

**Ordering information**

|                        |        |
|------------------------|--------|
| Orderable              | Yes    |
| Order-Unit             | Pieces |
| Minimum order quantity | 1      |
| Order Increment        | 1      |

**Supply Information**

|                                   |                |
|-----------------------------------|----------------|
| Weight (kg)                       | 0,793          |
| Packaging                         | Cardboard box  |
| Packaging dimensions (LxWxH) (mm) | 300 x 150 x 95 |