



PRE-24/R/LED/LINECT

Slave 2 watt, 24 Volt recess led luminaire, series Previs

Product Information

Type	PRE-24/R/LED/LINECT
Catalog number	34063020
Category_	Escape route lighting;Escape route signalisation
GTIN	08713812752853
GID	7TCA091130R0060
Serie	Previs
Warranty (Year)	5
Other	The luminaire is equipped with a light dimming circuit, the minimum output is in accordance with the standard



Characteristics

Power supply system	Central
Continuous operation	Yes
Mounting Method	Ceiling
Mounting form	Recess
Material housing	Plastic
Colour housing	White
Material cover	Plastic, transparent
Material	Polycarbonate
Colour	White
Length (mm)	292
Width (mm)	160
Height/depth (mm)	100
Built-in length (mm)	259
Built-in width (mm)	146
Built-in depth (mm)	120
Nominal voltage (V)	24
Voltage type	AC/DC
Monitoring equipment	None
With lamp	Yes
Lamp Type	Led
Lamp holder	Other
Lamp power (W)	2
Number of lamps	1
Light output in emergency operation (lm)	115
Average lifespan light source (hours)	100.000
Colour of light	White
CRI	60
Protection class	II
Degree of protection (IP)	40
With remote switch connection	No
Wiring system	Maintained / non-maintained circuit
Type of indicator	Single / double-sided
Labelling type	Insert sheet/plate
Recognition distance (m)	25
Circuit	Other
Power consumption maintained mode (W)	3,2 / 2,8
Apparent power consumption maintained	

Apparent power consumption maintenance mode (VA)	4,9 / 2,8
Nominal current (mA)	183 / 106
Inrush Current (A - 0.1ms)	7,3 / 4,5
Powerfactor	0,65
Temperature range (°C)	0 ~ +25

Article Details

Product class	Emergency luminaire
E-code	EC001957
Discount group	30405
Harmonized code	9405408440
GLN	8713812000008

Ordering information

Orderable	Yes
Order-Unit	Pieces
Minimum order quantity	1
Order Increment	1

Supply Information

Weight (kg)	1,179
Packaging	Cardboard box
Packaging dimensions (LxWxH) (mm)	307 x 136 x 167