

Serenga2  
EL2200W-M8/COM S  
7TCA305020R0171



Product type	
Function	Escape route lighting
Product type	Self-contained luminaire
Operating mode	Maintained and non-
Battery type	NiMH

Product information	
Operating time	8 h
Viewing distance	-
Functional testing	Naveo®Pro
Max. mounting height	5,5 m
Mounting	Wall
Mounting type	Surface mounted
Housing colour	White
Housing material	Aluminium

Technical data			
Width mm	150	Lamp type	LED
Height mm	35	Input voltage	220-240 V, 50 Hz
Length mm	150	Degree of protection	IP54
Weight g	960	Isolation class	II
Color temperature K	5600	Impact strength	-
Lumen output	-	Ambient temperature	5°C.....35°C

Trade mark CE

We reserve the right to make technical changes to the products and the content of this document at any time without notice. In the case of orders, the agreed qualities are decisive. ABB assumes no responsibility for any errors or omissions in this document. We reserve all rights in this document and the items and illustrations contained therein. Reproduction, disclosure to third parties or use of its content - including parts - is prohibited without the prior written consent of ABB.

© Copyright 2020 ABB All rights reserved.

Technical changes reserved