

产品认证证书

II型自愿认证

证书编号: CQC2003010304101933

发证日期: 2021年12月31日

有效期至: 2031年12月31日

委托人名称
及注册地址 ABB Electrification Sweden AB, Motor Starting & Safety
Motorgrand 20, 72161 Vasteras, Sweden

制造商名称
及注册地址 ABB Electrification Sweden AB, Motor Starting & Safety
Motorgrand 20, 72161 Vasteras, Sweden

生产企业名称
及生产地址 ABB Electrification Sweden AB, Motor Starting & Safety
Motorgrand 20, 72161 Vasteras, Sweden

产品名称和系列、
规格、型号 交流接触器
AF1350-30-*, AF1650-30-*, AF2050-30-*,
AF1350T-30-*, AF1650T-30-*, AF2050T-30-*, 规格参数详见附件

产品标准和技术要求 GB/T 14048.4-2020

认证模式 产品型式试验+初次工厂检查+获证后监督

上述产品符合 CQC12-000001-2020 认证规则的要求, 特发此证。

本证书为变更证书, 证书首次颁发日期: 2020年08月28日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

可通过扫描下方二维码或登录国家认监委网站 (www.cnca.gov.cn) 查验证书信息



授权签字人

签发

陈昕

谢肇煦



中国质量认证中心



<http://www.cqc.com.cn>

中国·北京·南四环西路188号9区 100070

电话: +86 10 83886666

C(2) 0124904

CERTIFICATE OF PRODUCT CERTIFICATION

TYPE II CQC CERTIFICATION

CERTIFICATE NO.: CQC2003010304101933

Valid from: Dec.31,2021

Valid until: Dec.31,2031

NAME AND REGISTERED ADDRESS OF THE APPLICANT ABB Electrification Sweden AB, Motor Starting & Safety
Motorgrand 20, 72161 Vasteras, Sweden

NAME AND REGISTERED ADDRESS OF THE MANUFACTURER ABB Electrification Sweden AB, Motor Starting & Safety
Motorgrand 20, 72161 Vasteras, Sweden

NAME AND LOCATION OF THE FACTORY ABB Electrification Sweden AB, Motor Starting & Safety
Motorgrand 20, 72161 Vasteras, Sweden

PRODUCT NAME, MODEL AND SPECIFICATION AC Contactor
AF1350-30-*, AF1650-30-*, AF2050-30-*,
AF1350T-30-*, AF1650T-30-*, AF2050T-30-*, See the Appendix

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS GB/T 14048.4-2020

TYPE OF CERTIFICATION SCHEMES Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC12-000001-2020.

Date of original issued: Aug.28,2020

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn



SIGN BY

陈昕

SIGNATURE

谢肇煦

CHINA QUALITY CERTIFICATION CENTRE



<http://www.cqc.com.cn>

Section 9, No. 188, Nansihuan Xilu, Beijing 100070 P.R. China

Tel: +86 10 83886666

C(2) 0124904

产品认证证书

II型自愿认证

证书编号: CQC2003010304101933

第1页 共3页

本证书及附件应同时使用, 信息查验说明见证书页

纸号: 124904

AF1350-30-*, AF1650-30-*, AF2050-30-*,
AF1350T-30-*, AF1650T-30-*, AF2050T-30-*,
Ui: 1000V;
Uimp: 8kV;
Ith: AF1350-30-*, AF1350T-30-*: 1350A,
AF1650-30-*, AF1650T-30-*: 1650A,
AF2050-30-*, AF2050T-30-*: 2050A;
使用类别, 额定电压, 额定电流见下表

Category	Ue	AF1350/ AF1350T	AF1650/ AF1650T	AF2050/ AF2050T
AC-1	1000V	1350A	1650A	2050A
AC-3	220V-230V-240V-380V-400V-415V-440V	860A	1060A	1060A
	500V	860A	970A	970A
	690V	800A	970A	970A
	1000V	375A	400A	425A

Us: AF1350-30-*, AF1650-30-*, AF2050-30-*: 100-250VAC/DC, 50Hz/60Hz;
AF1350T-30-*, AF1650T-30-*, AF2050T-30-*: 230-240V, 50Hz/60Hz;

极数: 3P;

使用类别: AC-1, AC-3;

配用辅助触头:

CAL18-11, CAL18-11B, CAL18-11RT: (CQC2003010304088244)

1NO1NC, 2NO2NC;

Ith: 16A;

AC-15: Ue/Ie: AC24-127V/6A, AC220-240V/4A, AC280-440V/3A, AC500-690V/2A;

DC-13: Ue/Ie: DC24V/6A, DC48V/2.8A, DC72V/1A, DC125V/0.55A, DC250V/0.3A;

CEL18-10, CEL18-01: (CQC2016010304912317)



中国质量认证中心



产品认证证书

II型自愿认证

证书编号: CQC2003010304101933

第 2 页 共 3 页

本证书及附件应同时使用, 信息查验说明见证书页

纸号: 124904

1NO,1NC;

Ith: 0.1A;

AC-14:Ue/Ie: AC24-125V/0.1A,DC-12:Ue/Ie:24-110V/0.1A;

型号解释:

Full type		AF1350T-30-11-70			
		1 (AF1350T)	2 (30)	3 (11)	4 (70)
Position	product	√	√		
	package label	√	√	√	√

1 = Name of series and size of contactor 接触器系列名称及大小

AF1350 = Basic model 基本型号

AF1350T = Basic model with delayed drop-out 带低电压穿越功能

AF1650 = Basic model 基本型号

AF1650T = Basic model with delayed drop-out 带低电压穿越功能

AF2050 = Basic model 基本型号

AF2050T = Basic model with delayed drop-out 带低电压穿越功能

2: Number of main contacts 主触头数量

30 = 3 NO- and 0 NC-contacts

3: Number of NO and NC auxiliary contacts 辅助功能(CAL18-11, CEL18-01 or CEL18-10)

00 = without auxiliary contact 无辅助触头

11 = 1 NO- and 1 NC-contacts (side mounted 侧装 CAL18-11)



中国质量认证中心



产品认证证书

II型自愿认证

证书编号: CQC2003010304101933

第 3 页 共 3 页

本证书及附件应同时使用, 信息查验说明见证书页

纸号: 124904

- 22 = 2 NO- and 2 NC-contacts (side mounted 侧装 2 pieces CAL18-11)
01 = 0 NO- and 1 NC-contacts (side-mounted 侧装 CEL18-01)
10 = 1 NO- and 0 NC-contacts (side-mounted 侧装 CEL18-10)

4: Control supply voltage code 线圈代号

70: $U_s = 100-250V$ a.c./d.c. with PLC-control

91: $U_s = 230-240V$ ac (only for T-version 仅对 T 型)



中国质量认证中心

