



产品认证证书

证书编号: CQC2008010302317033

申请人名称及地址

ABB Oy
Muottitie 2A FI-65320 VAASA, Finland

制造商名称及地址

ABB Oy
Muottitie 2A FI-65320 VAASA, Finland

生产企业名称及地址

ABB Oy (V054902)
Muottitie 2A FI-65320 VAASA, Finland

产品名称和系列、规格、型号

隔离开关
OT16F_, OT16FT_, OT16M_, OT25F_, OT25FT_, OT25M_, OT40F_, OT40FT_, OT40M_, OT40ML_;
详见参数附件

产品标准和技术要求

GB/T14048.3-2017

认证模式

型式试验+初始工厂检查+获证后监督

上述产品符合 CQC11-462141-2019 认证规则的要求, 特发此证。

发证日期: 2020 年 09 月 02 日 有效期至: 2024 年 12 月 10 日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

经中国合格评定国家认可委员会认可 CNAS C001-P

主任:

陆楠



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>

C 0334126



PRODUCT CERTIFICATE

CERTIFICATE NO.: CQC2008010302317033

NAME AND ADDRESS OF THE APPLICANT

ABB Oy
Muottitie 2A FI-65320 VAASA, Finland

NAME AND ADDRESS OF THE MANUFACTURER

ABB Oy
Muottitie 2A FI-65320 VAASA, Finland

NAME AND ADDRESS OF THE FACTORY

ABB Oy (V054902)
Muottitie 2A FI-65320 VAASA, Finland

PRODUCT NAME, MODEL AND SPECIFICATION

Switch-disconnector
OT16F_, OT16FT_, OT16M_, OT25F_, OT25FT_, OT25M_, OT40F_, OT40FT_, OT40M_, OT40ML_; See the Appendix

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T14048.3-2017

TYPE OF CERTIFICATION SCHEMES

Type testing of product + initial factory inspection + follow up factory inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC11-462141-2019 .

Valid from: Sep.02,2020

Valid until: Dec.10,2024

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Accredited by China National Accreditation Service for Conformity Assessment CNAS C001-P

President:

Lu Mei



CHINA QUALITY CERTIFICATION CENTRE

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China
<http://www.cqc.com.cn>

C 0334126



产品认证证书

附录

第 1 页 共 3 页

证书编号: CQC2008010302317033

纸号: 334126

OT16F_, OT16FT_, OT16M_, OT25F_, OT25FT_, OT25M_, OT40F_, OT40FT_, OT40M_,
OT40ML_

Uimp: 8kV;

Ui: 750V;

OT16F, OT16FT:

Ith: 25A

Ue/Ie: 415/500/690V/16A (AC-21A, AC-22A)

415/500V/16A, 690V/10A (AC-23A)

OT16M:

Ith: 25A

Ue/Ie: 415V/16A

OT25F, OT25FT:

Ith: 32A

Ue/Ie: 415/500/690V/25A (AC-21A, AC-22A)

415/500V/20A, 690V/11A (AC-23A)

OT25M:

Ith: 32A

Ue/Ie: 415V/25A (AC-21A, AC-22A)

415V/20A (AC-23A)

OT40F, OT40FT

Ith: 40A

Ue/Ie: 415/500/690V/40A (AC-21A, AC-22A)

415/500V/23A, 690V/12A (AC-23A)

OT40M:

Ith: 40A

Ue/Ie: 415V/40A (AC-21A, AC-22A)

415V/23A (AC-23A)

OT40ML:

注: 此附录与证书同时使用时有效。

主任: _____

陆梅



中国质量认证中心

中国·北京·南四环西路188号9区 100070

<http://www.cqc.com.cn>



产品认证证书

附录

第 2 页 共 3 页

证书编号: CQC2008010302317033

纸号: 334126

Ith: 40A

Ue/Ie: 400V/40A (AC-21A, AC-22A)

400V/23A (AC-23A)

Icm(峰值): 705A;

Icw: 500A/1s;

Iq: 400V/50kA (OT40ML), 415V/50kA (OT16M, OT25M, OT40M), 690V/50kA (OT16F/FT, OT2

5F/FT, OT40F/FT)

使用类别: AC-21A, AC-22A, AC-23A;

极数: 3P, 4P;

适用频率: 50/60Hz;

IP20 (仅对前面板)

型号解释:

注: 此附录与证书同时使用时有效。

主任:

陆梅



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>



产品认证证书

附录

第 3 页 共 3 页

证书编号: CQC2008010302317033

纸 号: 334126

OT	16	F	4	N2	
					Included accessories 包含附件 N1=Fourth pole on the left side, 带第四极位于开关左侧 N2=Fourth pole on the right side, 带第四极位于开关右侧 blank=basic 4th pole, 基础款第四极
					Number of poles 极数 3--3 poles 3 极 4--4 poles 4 极 6--6 poles 6 极 8--8 poles 8 极
					Mounting 安装方式 F Base& DIN-rail mounting 底板和 DIN 导轨安装 FT Door mounting 门上安装 M Base& DIN-rail mounting(415V rating, grey body) M 底板和 DIN 导轨安装(415V 等级, 灰色壳体) ML Base& DIN-rail mounting(400V rating, white body) ML 底板和 DIN 导轨安装(400V 等级, 白色壳体)
					Switch Size 电流等级(A) 16, 25, 40
					Switch disconnector 隔离开关型号

注: 此附录与证书同时使用时有效。

主任:

陆梅



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>