

产品认证证书

II型自愿认证

证书编号: CQC2008010304261926

发证日期: 2021年10月22日

有效期至: 2031年10月22日

委托人名称	ABB France
及注册地址	11 Rue d' Arsonval 69680, Chassieu, FRANCE
制造商名称	ABB 新会低压开关有限公司
及注册地址	广东省江门市新会区今古洲工业开发区
生产企业名称	ABB 新会低压开关有限公司
及生产地址	广东省江门市新会区今古洲工业开发区
产品名称和系列、规格、型号	接触器 UA26-30-01,UA26-30-10; Ui:1000V; Uimp:8kV; Ith:45A; Ue:AC230/240V,AC400/415V,AC440V,AC500/550V,AC690V; Ie:42A; 使用类别:AC-6b; IP20; 极数:3P; Us:(50Hz/60Hz)24V/24V,42V/42V,48V/48V,110V/110V-120V,220V-230V/230V-240V,230V-240V/240V-260V,380V-400V/400V-415V, 190V/220V,400V-415V/415V-440V; 配用的辅助触头:1NO,1NC,Ith:16A; Ui:690V; Uimp:8kV; AC-15:Ue/Ie:AC24-127V/6A,AC220-240V/4A,AC380-440V/3A,AC500V/2A,AC690V/2A; DC-13:Ue/Ie:DC24V/6A,DC48V/2.8A,DC72V/2A,DC125V/1.1A,DC250V/0.55A.
产品标准和技术要求	GB/T 14048.4-2020
认证模式	产品型式试验+初次工厂检查+获证后监督

上述产品符合 CQC12-000001-2020 认证规则的要求, 特发此证。

本证书为变更证书, 证书首次颁发日期: 2020年08月14日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

可通过扫描下方二维码或登录国家认监委网站 (www.cnca.gov.cn) 查验证书信息



授权签字人

签发

刘江

谢肇煦



中国质量认证中心



<http://www.cqc.com.cn>

中国·北京·南四环西路188号9区 100070

电话: +86 10 83886666

C(2) 0113636

CERTIFICATE OF PRODUCT CERTIFICATION

TYPE II CQC CERTIFICATION

CERTIFICATE NO.: CQC2008010304261926

Valid from: Oct.22,2021

Valid until: Oct.22,2031

NAME AND REGISTERED

ABB France

ADDRESS OF THE APPLICANT

11 Rue d' Arsonval 69680, Chassieu, FRANCE

NAME AND REGISTERED

ABB Xinhui Low Voltage Switchgear Co., Ltd.

ADDRESS OF THE

Jinguzhou Industrial Development Zone, Xinhui District, Jiangmen City, Guangdong Province,

MANUFACTURER

P.R.China

NAME AND LOCATION

ABB Xinhui Low Voltage Switchgear Co., Ltd.

OF THE FACTORY

Jinguzhou Industrial Development Zone, Xinhui District, Jiangmen City, Guangdong Province,
P.R.China

**PRODUCT NAME, MODEL
AND SPECIFICATION**

Contactor

UA26-30-01, UA26-30-10; Ui:1000V; Uimp:8kV; Ith:45A;

Ue:AC230/240V, AC400/415V, AC440V, AC500/550V, AC690V; Ie:42A; Utilization Category :AC-6b;
IP20; Poles :3P;

Us:(50Hz/60Hz)24V/24V, 42V/42V, 48V/48V, 110V/110V-120V, 220V-230V/230V-240V, 230V-240V
/240V-260V, 380V-400V/400V-415V, 190V/220V, 400V-415V/415V-440V; Attached Auxiliary

Contacts :1NO, 1NC; Ith:16A; Ui:690V; Uimp:8kV;

AC-15:Ue/Ie:AC24-127V/6A, AC220-240V/4A, AC380-440V/3A, AC500V/2A, AC690V/2A;

DC-13:Ue/Ie:DC24V/6A, DC48V/2.8A, DC72V/2A, DC125V/1.1A, DC250V/0.55A.

**THE STANDARDS AND
TECHNICAL REQUIREMENTS
FOR THE PRODUCTS**

GB/T 14048.4-2020

**TYPE OF CERTIFICATION
SCHEMES**

Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC12-000001-2020.

Date of original issued: Aug.14,2020

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn



SIGN BY

刘江

SIGNATURE

谢肇煦



CHINA QUALITY CERTIFICATION CENTRE



<http://www.cqc.com.cn>

Section 9, No. 188, Nansihuan Xilu, Beijing 100070 P.R. China

Tel: +86 10 83886666

C(2) 0113636