

产品认证证书

II型自愿认证

证书编号: CQC2014010302705508

发证日期: 2023 年 04 月 06 日
有效期至: 2031 年 08 月 30 日

委托人名称	ABB 新会低压开关有限公司
及注册地址	广东省江门市新会区今古洲工业开发区
制造商名称	ABB 新会低压开关有限公司
及注册地址	广东省江门市新会区今古洲工业开发区
生产企业名称	ABB 新会低压开关有限公司
及生产地址	广东省江门市新会区今古洲工业开发区
产品名称和系列、规格、型号	隔离开关 OT630, OT800, OTM630, OTM800 : Uimp: 12kV;Ui : 1140V ; Ith : 800A ; Ue : AC1140V;Ie : AC-23A : 400A ; AC-22A : 630A(OT630, OTM630),800A(OT800, OTM800) ;Icw :20kA/1s;Icm(峰值) :80kA;使用类别 :AC-22A, AC-23A;极数 :2P, 3P, 4P;频率 : 50/60Hz ; 型号解释见附件
产品标准和技术要求	GB/T 14048.3-2017
认证模式	产品型式试验+初次工厂检查+获证后监督

上述产品符合 CQC12-000001-2020 认证规则的要求, 特发此证。

本证书为变更证书, 证书首次颁发日期: 2020 年 08 月 14 日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

可通过扫描下方二维码或登录国家认监委网站 (www.cnca.gov.cn) 查验证书信息



授权签字人

刘江

签发

谢肇熙

中国质量认证中心



<http://www.cqc.com.cn>

中国·北京·南四环西路188号9区 100070

电话: +86 10 83886666

C(2) 0218715

CERTIFICATE OF PRODUCT CERTIFICATION

TYPE II CQC CERTIFICATION

CERTIFICATE NO.: CQC2014010302705508

Valid from: Apr.06,2023

Valid until: Aug.30,2031

**NAME AND REGISTERED
ADDRESS OF THE APPLICANT**

ABB Xinhui Low Voltage Switchgear Co.,Ltd.
Jinguzhou Industrial Development Zone, Xinhui District, Jiangmen City, Guangdong Province,
P.R.China

**NAME AND REGISTERED
ADDRESS OF THE
MANUFACTURER**

ABB Xinhui Low Voltage Switchgear Co.,Ltd.
Jinguzhou Industrial Development Zone, Xinhui District, Jiangmen City, Guangdong Province,
P.R.China

**NAME AND LOCATION
OF THE FACTORY**

ABB Xinhui Low Voltage Switchgear Co.,Ltd.
Jinguzhou Industrial Development Zone Xinhui Region, Jiangmen City, Guangdong Province,
P.R.China

**PRODUCT NAME, MODEL
AND SPECIFICATION**

Switch-disconnector
OT630, OT800, OTM630, OTM800 :Uimp: 12kV;Ui :1140V ;Ith :800A ;Ue :AC1140V;Ie :AC-23A :
400A ; AC-22A : 630A(OT630, OTM630),800A(OT800, OTM800) ; Icw : 20kA/1s;Icm(Peak) :
80kA;Utilization Category : AC-22A, AC-23A;Poles : 2P, 3P, 4P;Applicable frequency : 50/60Hz
GB/T 14048.3-2017

**THE STANDARDS AND
TECHNICAL REQUIREMENTS
FOR THE PRODUCTS**

**TYPE OF CERTIFICATION
SCHEMES**

Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC12-000001-2020.

Date of original issued: Aug.14,2020

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn



SIGN BY

刘江

SIGNATURE

谢肇煦



CHINA QUALITY CERTIFICATION CENTRE



<http://www.cqc.com.cn>

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China

Tel: +86 10 83886666

C(2) 0218715

产品认证证书

II型自愿认证

附 录

证书编号: CQC2014010302705508

第 1 页 共 1 页

纸 号: 218715

型号解释:

OT □ □ □ □ - 1140
1 2 3 4 5 6

1、隔离开关: OT(不带电动操作机构型)、OTM(带电动操作机构型);

2、额定电流: 630、800

3、适用标准: E (适用 IEC 标准)、U (适用 IEC/UL 标准)

4、极数及位置识别码:

OT 型识别码: 02, 03, 04, 20, 30, 40, 11, 12, 13, 21, 31, 22;

第一位数字表示在操作机构左边的极数

第二位数字表示在操作机构右边的极数

OTM 型识别码: 2: 操作机构右边 2 极; 3: 操作机构右边 3 极; 4: 操作机构右边 4 极

5、操作方式: P (配门板操作手柄及轴)、K (配直接操作手柄)、空白 (无操作手柄)

M24D (配 24VDC 电动操作机构)、M48D (配 48VDC 电动操作机构)

M110C (配 110VAC 电动操作机构)、M110V (配 110VAC/DC 电动操作机构)

M230C (配 230VAC 电动操作机构)、M230V (配 230VAC/DC 电动操作机构)

6、电压识别码: 1140 代表 1140VAC

注: 此附录与证书同时使用时有效。



中国质量认证中心

