

产品认证证书

II型自愿认证

证书编号: CQC2014010307677588

发证日期: 2022年03月24日

有效期至: 2032年03月23日

委托人名称 厦门 ABB 低压电器设备有限公司
及注册地址 厦门火炬高新区(翔安)产业区舩山西二路 881 号一层

制造商名称 厦门 ABB 低压电器设备有限公司
及注册地址 厦门火炬高新区(翔安)产业区舩山西二路 881 号一层

生产企业名称 厦门 ABB 低压电器设备有限公司
及生产地址 福建省厦门市火炬高新区(翔安)产业区舩山西二路 881 号

产品名称和系列、规格、型号 万能式断路器
E6.2H, E6.2V, E6.2H/f, E6.2V/f, E6.2S/E9; E6.2H/E9; E6.2X/E9; E6.2S/E9FS; E6.2H/E9FS; 详细型号及解释见附件

产品标准和技术要求 GB/T 14048.2-2020

认证模式 产品型式试验+初次工厂检查+获证后监督

上述产品符合 CQC12-000001-2020 认证规则的要求, 特发此证。

本证书为变更证书, 证书首次颁发日期: 2020 年 09 月 01 日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

可通过扫描下方二维码或登录国家认监委网站(www.cnca.gov.cn)查验证书信息



授权签字人

签发

罗妍

谢肇煦



中国质量认证中心



<http://www.cqc.com.cn>

中国·北京·南四环西路188号9区 100070

电话: +86 10 83886666

C(2) 0147471

CERTIFICATE OF PRODUCT CERTIFICATION

TYPE II CQC CERTIFICATION

CERTIFICATE NO.: CQC2014010307677588

Valid from: Mar.24,2022

Valid until: Mar.23,2032

NAME AND REGISTERED ADDRESS OF THE APPLICANT	ABB Xiamen Low Voltage Equipment Co., Ltd. 1st Floor, No. 881, FangShanXiEr Road, Xiang' An Industrial Area, Torch Hi-Tech Industrial Development Zone, Xiamen, Fujian, P.R. China
NAME AND REGISTERED ADDRESS OF THE MANUFACTURER	ABB Xiamen Low Voltage Equipment Co., Ltd. 1st Floor, No. 881, FangShanXiEr Road, Xiang' An Industrial Area, Torch Hi-Tech Industrial Development Zone, Xiamen, Fujian, P.R. China
NAME AND LOCATION OF THE FACTORY	ABB Xiamen Low Voltage Equipment Co., Ltd. No. 881, FangShanXiEr Road, Xiang' An Industrial Area, Torch Hi-Tech Industrial Development Zone, Xiamen, Fujian, P.R.China
PRODUCT NAME, MODEL AND SPECIFICATION	Air circuit breaker E6.2H, E6.2V, E6.2H/f, E6.2V/f, E6.2S/E9; E6.2H/E9; E6.2X/E9; E6.2S/E9FS; E6.2H/E9FS; See the appendix
THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS	GB/T 14048.2-2020
TYPE OF CERTIFICATION SCHEMES	Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC12-000001-2020.

Date of original issued: Sep.01,2020

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn



SIGN BY

罗妍

SIGNATURE

谢肇熙



CHINA QUALITY CERTIFICATION CENTRE



产品认证证书

II型自愿认证

证书编号: CQC2014010307677588

第 1 页 共 3 页

本证书及附件应同时使用, 信息查验说明见证书页

纸号: 147471

上报参数:

E6.2H, E6.2V, E6.2H/f, E6.2V/f, E6.2S/E9, E6.2H/E9, E6.2X/E9, E6.2S/E9FS, E6.2H/E9FS

Uimp:12kV;

Ui: 1000V;

Ue: AC220V, AC230V, AC380V, AC400V, AC415V, AC440V, AC500V, AC525V, AC660V, AC690V,
AC725V (E6.2S/E9, E6.2S/E9FS),

AC800V, 900V (E6.2H/E9, E6.2X/E9, E6.2H/E9FS);

Ie: 400A, 600A, 630A, 800A, 1000A, 1200A, 1250A, 1600A, 2000A, 2500A, 3000A, 3200A, 3600A,
4000A, 5000A, 6000A, 6300A;

过电流脱扣器类型: 电子式;

Ics, Icu 和 Icw 见下表

		E6.2H E6.2H/f	E6.2V E6.2V/f	E6.2S/E9	E6.2H/E9	E6.2X/E9	E6.2S/E9 FS	E6.2H/E9 FS
Icu 220/230/380/400/415Vac	[kA]	100	150	-	-	-	-	-
Icu 440Vac	[kA]	100	150	-	-	-	-	-
Icu 500/525Vac	[kA]	100	130	-	-	-	-	-
Icu 660/690Vac	[kA]	100	100	-	-	-	-	-
Icu 725Vac	[kA]	-	-	70	-	-	70	-
Icu 800Vac	[kA]	-	-	-	90	100	-	90
Icu 900Vac	[kA]	-	-	-	75	90	-	75
Ics 220/230/380/400/415Vac	[kA]	100	150	-	-	-	-	-
Ics 440Vac	[kA]	100	150	-	-	-	-	-
Ics 500/525Vac	[kA]	100	130	-	-	-	-	-
Ics 660/690Vac	[kA]	100	100	-	-	-	-	-
Ics 725Vac	[kA]	-	-	70	-	-	70	-
Ics 800Vac	[kA]	-	-	-	90	100	-	90
Ics 900Vac	[kA]	-	-	-	75	90	-	75
Icw 1s 690Vac	[kA]	100	100	-	-	-	-	-
Icw 1s 725Vac	[kA]	-	-	70	-	-	35	-
Icw 1s 800/900Vac	[kA]	-	-	-	75	90	-	35

适用频率: 50/60Hz;

适用于隔离;

选择性类别: B 类;

极数: 3P, 4P

配用的辅助触头: (COC21107322161)

2NO2NC, 4NO4NC, 6NO6NC, 15NO15NC



中国质量认证中心



产品认证证书

II型自愿认证

证书编号: CQC2014010307677588

第 2 页 共 3 页

本证书及附件应同时使用, 信息查验说明见证书页

纸号: 147471

lth: 16A;

AC-12: Ue/Ie: AC250V/16A、AC125V/16A、AC250V/10A、AC125V/10A、AC250V/8A、AC125V/8A、
AC250V/6A、AC125V/6A、AC400V/3A;

DC-12: Ue/Ie: DC250V/0.3A、DC125V/0.6A;

配用的辅助触头(本体):

2NO2NC, 4NO4NC, 6NO6NC, 15NO15NC;

lth: 16A;

AC-12: Ue/Ie: 400 V / 3A;

AC-14: Ue/Ie: 400V/3A, 250V/10A;

DC-12: Ue/Ie: 24V/0.1A;

DC-13: Ue/Ie: 250V / 0.15A; 125V / 0.3A

符合附录 N 的电子附件:

闭合线圈: YC;

Us: 24VAC/DC, 30 VAC/DC, 48 VAC/DC, 60 VAC/DC, 110-120 VAC/DC, 120-127 VAC/DC, 220-240
VAC/DC, 240-250 VAC/DC, 380-400 VAC, 415-440 VAC, 480-500 VAC 50/60Hz;

欠压脱扣器: YU;

Us: 24VAC/DC, 30 VAC/DC, 48 VAC/DC, 60 VAC/DC, 110-120 VAC/DC, 120-127 VAC/DC, 220-240
VAC/DC, 240-250 VAC/DC, 380-400 VAC, 415-440 VAC, 480-500 VAC 50/60Hz;

分励脱扣器: YO;

Us: 24VAC/DC, 30 VAC/DC, 48 VAC/DC, 60 VAC/DC, 110-120 VAC/DC, 120-127 VAC/DC, 220-240
VAC/DC, 240-250 VAC/DC, 380-400 VAC, 415-440 VAC, 480-500 VAC 50/60Hz;

型号解释:

Emax 2 系列万能式断路器



中国质量认证中心



产品认证证书

II型自愿认证

证书编号: CQC2014010307677588

第 3 页 共 3 页

本证书及附件应同时使用, 信息查验说明见证书页

纸号: 147471

E6.2	S/H/V/X	blank or /E9	blank or /f	blank or FS	400 - 6300	额定电流
						FS: 快速分断版本 空白: 常规版本
						四级断路器的中性极载流能力 /f: 100% 空白: 50%
						/E9: IEC 900Vac 版本 空白: IEC 690Vac版本
						分断能力等级 X: 超高层 V: 极高层 H: 高层 S: 标准型
						E6.2: Emax2系列断路器型号 E6.2



中国质量认证中心

