

产品认证证书

II型自愿认证

证书编号: CQC2015010304824714

发证日期: 2022年02月15日

有效期至: 2032年02月15日

委托人名称 ABB France
及注册地址 11 Rue d' Arsonval 69680, Chassieu, FRANCE

制造商名称 ABB France
及注册地址 11 Rue d' Arsonval 69680, Chassieu, FRANCE

生产企业名称 ABB France
及生产地址 11 Rue d' Arsonval 69680, Chassieu, FRANCE

产品名称和系列、规格、型号 接触器
AF*40-30-**-**, AF40-40-**-**, AF40-22-**-**, AF*52-30-**-**, AF52-40-**-**, AF*65-30-**-** ; 详见附件

产品标准和技术要求 GB/T 14048.4-2020

认证模式 产品型式试验+初次工厂检查+获证后监督

上述产品符合 CQC12-000001-2020 认证规则的要求, 特发此证。

本证书为变更证书, 证书首次颁发日期: 2020年08月21日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

可通过扫描下方二维码或登录国家认监委网站 (www.cnca.gov.cn) 查验证书信息



授权签字人

签发

陈昕

谢肇熙



中国质量认证中心



<http://www.cqc.com.cn>

中国·北京·南四环西路188号9区 100070

电话: +86 10 83886666

C(2) 0138149

CERTIFICATE OF PRODUCT CERTIFICATION

TYPE II CQC CERTIFICATION

CERTIFICATE NO.: CQC2015010304824714

Valid from: Feb.15,2022

Valid until: Feb.15,2032

NAME AND REGISTERED ADDRESS OF THE APPLICANT ABB France
11 Rue d' Arsonval 69680, Chassieu, FRANCE

NAME AND REGISTERED ADDRESS OF THE MANUFACTURER ABB France
11 Rue d' Arsonval 69680, Chassieu, FRANCE

NAME AND LOCATION OF THE FACTORY ABB France
11 Rue d' Arsonval 69680, Chassieu, FRANCE

PRODUCT NAME, MODEL AND SPECIFICATION Contactor
AF*40-30-**-**, AF40-40-**-**, AF40-22-**-**, AF*52-30-**-**, AF52-40-**-**, AF*65-30-**-** ;
See the appendix

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS GB/T 14048.4-2020

TYPE OF CERTIFICATION SCHEMES Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC12-000001-2020.

Date of original issued: Aug.21,2020

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn



SIGN BY

陈昕

SIGNATURE

谢肇煦



CHINA QUALITY CERTIFICATION CENTRE



<http://www.cqc.com.cn>

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China

Tel: +86 10 83886666

C(2) 0138149

产品认证证书

II型自愿认证

证书编号: CQC2015010304824714

第 1 页 共 5 页

本证书及附件应同时使用, 信息查验说明见证书页

纸号:

AF*40-30-**-**, AF40-40-**-**, AF40-22-**-**,
AF*52-30-**-**, AF52-40-**-**, AF*65-30-**-**

Ui: 690V;

Uimp: 6kV;

Ith: 105A;

AF*40-30:

AC-1: Ue/Ie: 690V/70A;

AC-3/AC-3e: Ue/Ie: 220-440V/40A, 500V/35A, 690V/25A;

AC-4: Ue/Ie: 220-500V/35A, 690V/25A;

AC-8a: Ue/Ie: 400V/53A;

AF40-40:

AC-1: Ue/Ie: 690V/70A;

AC-3/AC-3e: Ue/Ie: 220-440V/40A, 500V/35A, 690V/25A;

AC-4: Ue/Ie: 220-500V/35A, 690V/25A;

AF40-22:

AC-1: Ue/Ie: 690V/70A;

AC-3/AC-3e: Ue/Ie: 220-440V/40A, 500V/35A, 690V/25A;

AC-4: Ue/Ie: 220-500V/35A, 690V/17A;

AF*52-30:

AC-1: Ue/Ie: 690V/100A;

AC-3/AC-3e: Ue/Ie: 220-440V/53A, 500V/45A, 690V/35A;

AC-4: Ue/Ie: 220-500V/45A, 690V/28A;

AC-8a: Ue/Ie: 400V/70A;

AF52-40:

AC-1: Ue/Ie: 690V/100A;

AC-3/AC-3e: Ue/Ie: 220-440V/53A, 500V/45A, 690V/35A;

AC-4: Ue/Ie: 220-500V/45A, 690V/28A;

AF*65-30:



中国质量认证中心

产品认证证书

II型自愿认证

证书编号: CQC2015010304824714

第 2 页 共 5 页

本证书及附件应同时使用, 信息查验说明见证书页

纸号:

AC-1: Ue/Ie: 690V/105A;

AC-3/AC-3e: Ue/Ie: 220-440V/65A, 500V/55A, 690V/39A;

AC-4: Ue/Ie: 220-500V/52A, 690V/31A;

AC-8a: Ue/Ie: 400V/85A;

Us: 24-60V 50/60Hz 20-60V DC, 24-60V 50/60Hz, 48-130V 50/60Hz-DC,
100-250V 50/60Hz-DC, 250-500V 50/60Hz-DC ;

极数: 3P, 4P;

IP10 ;

配用的辅助触头: (外置)

CA4-***, CAT4-***, VE4 (CQC2013010304651497);

CAL4-**, CA4-**, CC4-** (CQC2011010304496319);

1NO, 1NC, 2NO, 2NC;

Ith: 16A;

AC-15: Ue/Ie: AC500-690V/2A, AC380-440V/3A, AC220-40V/4A, AC24-127V/6A;

DC-13: Ue/Ie: DC600V/0.1A, DC500V/0.13A, DC220-250V/0.27A,

DC110-125V/0.55A, DC72V/1A, DC48V/2.8A, DC24V/6A;



中国质量认证中心

产品认证证书

II型自愿认证

证书编号: CQC2015010304824714

第 3 页 共 5 页

本证书及附件应同时使用, 信息查验说明见证书页

纸号:

型号解释:

Example 例如: AFS40-30-00-11					
AF	S	80	-30	-00	-11
I	II	III	IV	V	VI

I – Name of series 系列名称

AF series 系列

II – Application 大小

Blank – Standard applications

S contactor for safety application

III – Range size 大小

40, 52, 65

IV – Number of main contacts 主触头数量

22 – 2 Normally Opened and 2 Normally Closed main poles.

30 – 3 Normally Opened and 0 Normally Closed main poles.

40 – 4 Normally Opened and 0 Normally Closed main poles.

V – Number of auxiliary contacts 辅助触头数量

00 – No auxiliary pole provided.

11 – One Normally Opened and one Normally Closed auxiliary poles.

22 – Two Normally Opened and two Normally Closed auxiliary poles (AFS only available with this configuration).



中国质量认证中心

产品认证证书

II型自愿认证

证书编号: CQC2015010304824714

第 4 页 共 5 页

本证书及附件应同时使用, 信息查验说明见证书页

纸号:

VI - Coil code 线圈代号

Control voltage		Coil code
50/60Hz	DC	
24-60V		41
24-60V	20-60V	11
48-130V	48-130V	12
100-250V	100-250V	13
250-500	250-500	14



中国质量认证中心

产品认证证书

II型自愿认证

证书编号: CQC2015010304824714

第 5 页 共 5 页

本证书及附件应同时使用, 信息查验说明见证书页

纸号:

List of type

DESIGNATION
AF40-30-00-xx
AF40-30-11-xx
AF40-30-22-xx
AFS40-30-22-xx
AF40-40-00-xx
AF40-22-00-xx
AF52-30-00-xx
AF52-30-11-xx
AF52-30-22-xx
AFS52-30-22-xx
AF52-40-00-xx
AF65-30-00-xx
AF65-30-11-xx
AF65-30-22-xx
AFS65-30-22-xx



中国质量认证中心