



产品认证证书

证书编号: CQC2016010302932422

申请人名称及地址

ABB Oy

Muottitie 2A FI-65320 VAASA, Finland

制造商名称及地址

ABB Oy

Muottitie 2A FI-65320 VAASA, Finland

生产企业名称及地址

ABB Oy (V054902)

Muottitie 2A FI-65320 VAASA, Finland

产品名称和系列、规格、型号

隔离开关

OT3200_, OT4000_: Uimp: 12kV; Ui: 1000V; Ith: 3200A(OT3200), 3200A(OT3200 W8), 3800A(OT4000), 4000A(OT4000 W8); Ie: 3200A(OT3200), 3200A(OT3200 W8), 3800A(OT4000), 4000A(OT4000 W8); Ue: 415V; Icm(峰值): 176kA(AC415/690V), 220kA(AC415/690V, OT4000 W8); Icw: 65kA/1s, 80kA/0.5s(AC415/690V, OT3200); 80kA/1s(AC415/690V, OT4000); 80kA/1s, 100kA/0.5s(AC415/690V, OT4000 W8, 3P, 4P); 使用类别: AC-21B, AC-22B; 极数: 2P, 3P, 4P; 适用频率: 50/60Hz; IP20(仅对前面板); 型号解释见附件

产品标准和技术要求

GB/T14048. 3-2017

认证模式

型式试验+初始工厂检查+获证后监督

上述产品符合 CQC11-462141-2019 认证规则的要求, 特发此证。

发证日期: 2020 年 09 月 02 日 有效期至: 2021 年 12 月 29 日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

主任:

陆楠



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>

C 0334192



PRODUCT CERTIFICATE

CERTIFICATE NO.: CQC2016010302932422

NAME AND ADDRESS OF THE APPLICANT

ABB Oy
Muottitie 2A FI-65320 VAASA, Finland

NAME AND ADDRESS OF THE MANUFACTURER

ABB Oy
Muottitie 2A FI-65320 VAASA, Finland

NAME AND ADDRESS OF THE FACTORY

ABB Oy (V054902)
Muottitie 2A FI-65320 VAASA, Finland

PRODUCT NAME, MODEL AND SPECIFICATION

Switch-Disconnecter

OT3200_, OT4000_:Uimp: 12kV;Ui: 1000V;lth: 3200A(OT3200),3200A(OT3200 W8),3800A(OT4000),4000A(OT4000 W8);Ie: 3200A(OT3200),3200A(OT3200 W8),3800A(OT4000),4000A(OT4000 W8);Ue: 415V;lcm(Peak): 176kA(AC415/690V),220kA(AC415/690V,OT4000 W8);lcr: 65kA/1s, 80kA/0.5s(AC415/690V,OT3200);80kA/1s(AC415/690V, OT4000);80kA/1s, 100kA/0.5s(AC415/690V,OT4000 W8,3P,4P);Utilization Category: AC-21B, AC-22B;Poles: 2P, 3P, 4P;Applicable frequency: 50/60Hz;IP20(only for front panels);See the appendix

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T14048.3-2017

TYPE OF CERTIFICATION SCHEMES

Type testing of product + initial factory inspection + follow up factory inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC11-462141-2019 .

Valid from: Sep.02,2020

Valid until: Dec.29,2021

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

President:

Lu Mei



CHINA QUALITY CERTIFICATION CENTRE

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China
<http://www.cqc.com.cn>

C 0334192



产品认证证书

附录

第 1 页 共 1 页

证书编号: CQC2016010302932422

纸 号: 334192

型号解释:

OT	3200	E	13	H	W8	P
						P = handle & shaft included 带门上安装手柄和轴 K = direct handle 带直接安装手柄 Blank = without handle & shaft 不带手柄和轴
						W8 = phase distance 185mm 宽相间距 185mm Blank = phase distance 145mm 相间距 145mm
						H = silver layer 20 μ 镀银 20 μ Blank = silver layer 7 μ 镀银 7 μ
						Poles (according to side of mechanism) 极数 3 poles (3 极)- 12, 21, 03, 30 4 poles (4 极)- 22, 04, 40 1. number = number of poles on left side 第一位数字表示在机械结构左边的极数 2. number = number of poles in right side 第一位数字表示在机械结构右边的极数
						Structure 操作方式 E = used in IEC types 正面操作-IEC 标准
						Switch size 电流等级(A) 3200 & 4000
						Switch disconnecter 隔离开关型号

注: 此附录与证书同时使用时有效。

主任:

陆梅

中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>

